


# SF5350



## Flow sensor for connection to an evaluation unit

SFD10ADB /6M



1 Internal thread M18 x 1,5



### Product characteristics

Probe length L	[mm]	45
Process connection		M18 x 1,5 internal thread

### Application

Application		high-temperature range
Media		Liquids; Gases
Medium temperature	[°C]	-25...80
Pressure rating	[bar]	300

### Electrical data

Connection to control monitor		VS3000
-------------------------------	--	--------

### Measuring/setting range

Probe length L	[mm]	45
Liquids		
Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60
Gases		
Setting range	[cm/s]	200...3000
Greatest sensitivity	[cm/s]	200...800

### Accuracy / deviations

Temperature gradient	[K/min]	300
----------------------	---------	-----

### Response times

Response time	[s]	1...10
---------------	-----	--------

### Operating conditions

Protection		IP 67
------------	--	-------

### Tests / approvals

Shock resistance	DIN IEC 68-2-27	40 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	10 g (55...2000 Hz)
MTTF	[years]	8213

# SF5350



## Flow sensor for connection to an evaluation unit


SFD10ADB /6M

Mechanical data	
Weight [g]	413.5
Housing	for adapter
Dimensions [mm]	M18 x 1.5
Thread designation	M18 x 1.5
Materials	stainless steel (1.4404 / 316L)
Materials (wetted parts)	stainless steel (1.4404 / 316L); O-ring: FKM 80 Shore A
Process connection	M18 x 1,5 internal thread

Remarks	
Pack quantity	1 pcs.

**Electrical connection**  
Cable: 6 m, PUR; Maximum cable length: 100 m; 5 x 0.34 mm<sup>2</sup>

### Connection



	Core colours :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey