

## Workplace mat made of SBR/nitrile rubber mixture, hard-wearing

Checker plate structure, height 12.5 mm

### Application:

Suitable for work areas subject to high temperatures, and also for workbenches, assembly and laboratory areas, packing tables or inspection stands.

### Execution:

- Black closed mat, surface in checker plate design allows easy turning on the spot, made of SBR/nitrile rubber mixture
- Temperature-resistant from -30 °C to +70 °C
- Dovetail connections mean that any length can be achieved (width of 700 mm)
- With bevelled edges on 3 sides
- Good resistance against oils and greases
- Slip prevention R9 according to EN 13552
- Material: Natural rubber/25% nitrile mixture

### Advantage:

- Effortless design of production lines thanks to dovetail connection



<b>Art. no.</b>	<b>50225 320</b>
<b>Manufacturer Part Number</b>	CL010001
<b>Surface structure</b>	Stud plate / closed
<b>Material</b>	Nitrile rubber
<b>Length</b>	800 mm
<b>Width</b>	700 mm
<b>Material thickness</b>	12.5 mm
<b>Mat design</b>	End piece
<b>Resistance against</b>	Oil, Fats, Petrol, Coolant
<b>Min. temperature resistance</b>	-30 °C
<b>Max. temperature resistance</b>	70 °C
<b>Suitable for wet areas</b>	Yes
<b>Antistatic</b>	No
<b>Anti-fatigue</b>	Yes
<b>Non-slip</b>	Yes
<b>Compliant with REACH</b>	Yes
<b>Colour</b>	Black
<b>Gross Weight</b>	4.645 kg
<b>Product Group</b>	5AD

### EAN

5060087951676