

SITOP MODULAR 40 STABILIZED POWER SUPPLY INPUT: 400-500 V 3 AC OUTPUT: 24 V DC/40 A



Technical specifications

Product	SITOP modular
Power supply, type	24 V/40 A

Input

Input	3-phase AC
Rated voltage value V_{in} rated	400 ... 500 V
Voltage range AC	320 ... 550 V
<ul style="list-style-type: none"> Note 	Starting from $V_{in} > 340$ V
Wide-range input	Yes
Overvoltage resistance	$2.3 \times V_{in}$ rated, 1.3 ms
Mains buffering at I_{out} rated, min.	6 ms; at $V_{in} = 400$ V
Rated line frequency	50 ... 60 Hz
Rated line range	47 ... 63 Hz
Input current at rated input voltage 400 V Rated value	2.2 A
Switch-on current limiting (+25 °C), max.	70 A
I^2t , max.	2.8 A ² ·s
Built-in incoming fuse	none
Protection in the mains power input (IEC 898)	Required: 3-pole connected miniature circuit breaker 10 ... 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)

Output

Output	Controlled, isolated DC voltage
Rated voltage V_{out} DC	24 V
Total tolerance, static \pm	3 %

Static mains compensation, approx.	0.1 %
Static load balancing, approx.	0.2 %
Residual ripple peak-peak, max.	100 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV
Adjustment range	24 ... 28.8 V
Product function Output voltage adjustable	Yes
Output voltage setting	via potentiometer; max. 960 W
Status display	Green LED for 24 V OK
Signaling	via signaling module (6EP1961-3BA10)
On/off behavior	No overshoot of Vout (soft start)
Startup delay, max.	2.5 s
Voltage increase time of the output voltage maximum	500 ms
Rated current value I _{out} rated	40 A
Current range	0 ... 40 A
• Note	+60 ... +70 °C: Derating 2%/K
Active power supplied typical	960 W
Constant overload current on short-circuiting during the start-up typical	46 A
Short-term overload current at short-circuit during operation typical	120 A
Duration of overloading capability for excess current at short-circuit during operation	25 ms
Parallel switching for enhanced performance	Yes; switchable characteristic
Numbers of parallel switchable units for enhanced performance	2

Efficiency

Efficiency at V _{out} rated, I _{out} rated, approx.	90 %
Power loss at V _{out} rated, I _{out} rated, approx.	106 W

Closed-loop control

Dynamic mains compensation (V _{in} rated ±15 %), max.	1 %
Dynamic load smoothing (I _{out} : 50/100/50 %), U _{out} ± typ.	2 %
Load step setting time 50 to 100%, typ.	4 ms
Load step setting time 100 to 50%, typ.	4 ms
Setting time maximum	10 ms

Protection and monitoring

Output overvoltage protection	< 35 V
Current limitation, typ.	46 A
Property of the output Short-circuit proof	Yes
Short-circuit protection	Alternatively, constant current characteristic approx. 46 A or latching shutdown
Enduring short circuit current RMS value typical	46 A

Overload/short-circuit indicator	LED yellow for "overload", LED red for "latching shutdown"
----------------------------------	--

Safety

Primary/secondary isolation	Yes
Galvanic isolation	Safety extra-low output voltage U _{out} acc. to EN 60950-1 and EN 50178
Protection class	Class I
Leakage current maximum	3.5 mA
CE mark	Yes
UL/CSA approval	Yes
UL/cUL (CSA) approval	UL-Listed (UL 508), File E197259, CSA (CSA C22.2 No. 14, CSA C22.2 No. 107.1)
Explosion protection	ATEX (EX) II 3G Ex nA nC IIC T3 Gc; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T3
Certificate of suitability IECEx	No
Certificate of suitability NEC Class 2	No
FM approval	-
CB approval	No
Marine approval	-
Degree of protection (EN 60529)	IP20

EMC

Emitted interference	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2
Noise immunity	EN 61000-6-2

Operating data

Ambient temperature during operation	0 ... 70 °C
• Note	with natural convection
Ambient temperature during transport	-40 ... +85 °C
Ambient temperature during storage	-40 ... +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation

Mechanics

Connection technology	screw-type terminals
Connections Supply input	L1, L2, L3, PE: 1 screw terminal each for 0.2 ... 4 mm ² single-core/finely stranded
Connections Output	+, -: 2 screw terminals each for 0.33 ... 10 mm ²
Connections Auxiliary	-
Width of the enclosure	240 mm
Height of the enclosure	125 mm
Depth of the enclosure	125 mm
Weight, approx.	3.2 kg
Product property of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x15

Electrical accessories	Buffer module, signaling module
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)