

Part Number	Number of Conductors (incl. ground)	Nominal Outer Diameter (in) (mm)		Copper Weight (lbs/mft)	Approx. Weight (lbs/mft)	SKINTOP® Non-Metallic PG Thread	Part Number	Number of Conductors (incl. ground)	Nominal Outer Diameter (in) (mm)		Copper Weight (lbs/mft)	Approx. Weight (lbs/mft)	SKINTOP® Non-Metallic PG Thread
18 AWG (7 strand)							12 AWG (19 strand)						
201803	3	0.286	7.3	16	46	S2111	201203	3	0.381	9.7	64	106	S2113
201804	4	0.307	7.8	21	56	S2111	201204	4	0.413	10.5	85	110	S2113
201805	5	0.332	8.4	26	67	S2111	201205	5	0.451	11.5	106	164	S2113
201807	7	0.358	9.1	37	84	S2111	201207	7	0.490	12.4	149	217	S2116
201809	9	0.411	10.4	48	106	S2113	201212	12	0.673	17.1	255	378	S2129
201812	12	0.458	11.6	63	133	S2116	201216	16	0.743	18.9	341	488	S2129
201818	18	0.562	14.3	95	204	S2121	10 AWG (19 strand)						
201819	19	0.562	14.3	101	211	S2121	201003	3	0.433	11.0	102	150	S2116
201825	25	0.636	16.2	132	267	S2121	201004	4	0.471	12.0	136	193	S2116
16 AWG (7 strand)							201005	5	0.516	13.1	170	236	S2121
201603	3	0.312	7.9	26	59	S2111	201007	7	0.594	15.1	238	333	S2129
201604	4	0.336	8.5	34	73	S2111	8 AWG (19 strand)						
201605	5	0.365	9.3	43	87	S2111	200804	4	0.621	15.8	217	320	S2121
201607	7	0.394	10.0	60	112	S2113	200805	5	0.680	17.3	271	392	S2129
201608	8	0.424	10.8	68	127	S2113	6 AWG (19 strand)						
201609	9	0.455	11.6	77	142	S2116	200604	4	0.756	19.2	343	484	S2129
201612	12	0.508	12.9	103	180	S2121	200605	5	0.871	22.1	429	629	S2129
201616	16	0.593	15.1	137	249	S2121							
201618	18	0.622	15.8	154	275	S2129							
201619	19	0.622	15.8	162	284	S2129							
201625	25	0.706	17.9	214	363	S2129							
14 AWG (19 strand)													
201403	3	0.344	8.7	40	78	S2111							
201404	4	0.372	9.4	54	98	S2111							
201405	5	0.405	10.3	67	118	S2113							
201407	7	0.439	11.2	94	154	S2113							
201409	9	0.509	12.9	121	197	S2121							
201412	12	0.602	15.3	161	269	S2129							
201418	18	0.697	17.7	242	381	S2129							
201419	19	0.697	17.7	255	396	S2129							
201425	25	0.794	20.2	335	508	S2129							

Recommended SKINTOP® assumes minimal OD variance. Additional configurations are available; please see our SKINTOP® section. If not otherwise specified, all values relating to the product are nominal values. For current information go to our website.