




Measuring leads

MLN 100/2,5 Au



Product	MLN 100/2,5 Au
description	Measuring lead, at either end 4 mm diameter plug with caged spring and 4 mm diameter socket for tower construction. Gold-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, grip and lead shatter-proof. Built in colour indicator for easy identification of insulation damages.
article-no. / *colour	9340637xx  Au
drawing	
technical data	
rated voltage ⁽¹⁾	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	CAT I
rated current ⁽¹⁾ (consider derating curve)	32 A
material plug	brass, tin plated
housing material	PA
temperature range acc. To IEC61010 ⁽²⁾	-15 °C to +70 °C
inflammability class acc. to UL 94	V-2
cable length	100 cm
conductor size	2,5 mm ²
cable material	PVC

4 mm system

contact resistance	12 mOhm
standard	IEC 61010

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges
stand: 15.06.2016