

SSRC clamping holder, positive, right

For longitudinal turning with CC indexable insert

ATORN[®]

Application

For longitudinal turning with CC indexable insert, 80°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 75°, tip angle 90°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces
- Very good surface quality for medium infeed and finishing



Art. no.	17830 804
ISO name	SCRC R/L 12 12 F09
Shaft height	12 mm
Shank width	12 mm
Length	80 mm
Length of head	20 mm
Programming size	13 mm
Suitable for indexable inserts	CC.. 09T3..
Tool design	Right

EAN-Code

4050293562668