


For In-Circuit- and Functional Test (ICT/FCT)

F111

Centers 1,27 mm/50 mil

	Current	Temperature
Standard	1,5 A	-20°... +80° C
H-Version	1,5 A	-40°... +250° C

Especially suited for testing loaded SMT boards. The projection height is identical to the spring contact probes F109 (40 mil). The receptacle is also available with 550 mm preattached stranded wire (0,05 mm²/AWG28), order number H111LI or 550 mm insulated solid wire (0,05 mm²/AWG30), order number H111DR. Delivery time on request.



Mechanical Specifications

Working Travel: 2,0 mm
 Full Travel: 2,5 mm
 Preload: 20 cN
 Spring Force at Working Travel: 85 cN ±20%
 On Request: 40 cN ±20%,
 95 cN ±20% (high temperature)
 Mechanical Life: 1,5 mill. cycles
 Pointing Accuracy: ±0,09 mm

Electrical Specifications

Maximum Continuous Current: 1,5 A
 Typical Probe Resistance: 65 mOhm

Materials and Finishes

Plunger: see Tip Style
 Barrel: Nickel Silver, Gold plated
 Spring: Music Wire, Silver plated
 Receptacle: Nickel Silver, Gold plated

Projection Height

H111CR	H111LA	H111LA1
4,0 mm	4,0 mm	8,0 mm

Order Example

Type: **F111**
 Tip Diameter: **01S**
 Spring Force: **053**
 Tip Style: **N**
 Material: **095**
 Plunger Finish: **H**
 Special Version (optional): **H**

Material: S = Steel
Tip Diameter: 0,53 mm = 053
Plunger Finish: N = Nickel plated, L = Longtime gold plated, R = Rhodium plated
Special Version: H = High Temperature Probe
Receptacle: Order Number see drawing

Plunger Tip Style, Material, Finish and Tip Diameter

01 Steel; N Ø 0,53 mm	03 Steel; N Ø 0,53 mm	05 Steel; L Ø 0,9 mm	07 Steel; N Ø 0,9 mm	09 Steel; N Ø 0,9 mm
12 Steel; L Ø 0,9 mm	14 Steel; N Ø 0,9 mm	18 Steel; N, R Ø 0,53 mm	21 Steel; N Ø 0,53 mm	