# multicomp PRO

RoHS

**Compliant** 



## Specifications:

: Metal Flim
: 1/8W (0.125W)
: 200V or $\sqrt{PxR}$ whichever lesser
: 400V or 2.5 $\sqrt{PxR}$ whichever lesse
: 200V
: 70°C
: -55°C to +155°C
: ±2%
: 2.2Ω to 1MΩ

## **Power Rating**

Resistors shall have a power rating based on continuous full load operation at an ambient temperature of 70°C. For temperature in excess of 70°C, the load shall be derated as shown in the below figure.

### Voltage Rating:

Resistors shall have a rated direct-current (DC) continuous working voltage or an approximate sine-wave root-mean-square (RMS) alternating-current (AC) continuous working voltage at commercialline frequency and waveform curresponding to the power rating , as determined from the following formula:

$$\mathsf{RCWV} = \sqrt{\mathsf{P} \times \mathsf{R}}$$

Were : RCWV = Rated DC or RMS AC continuous working voltage at commercial-line frequency and waveform (V)

P = Power Rating (W)

In no case shall the rated DC or RMS AC continuous working voltage be greater than the applicable maximum value.



Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

# multicomp PRO

#### Construction



No	Name	Material		
1	Basic Body	Rod Type Ceramics		
2	Resistance Film	Metal Film		
3	End Cap	Steel (Tin plated iron surface)		
4	Lead Wire	Annealed copper wire coated with tin		
5	Joint	By Welding		
6	Coating	Non-Flame Paint (Colour: Green Meeting UL94V-0 Standard)		
7	Colour Code	Epoxy Resin		

## **Metal Film Fixed Resistors**

Characteristics	Limits	Test Methods( JIS C 5201-1 )
DC. resistance	Must be within the specified tolerance	The limit of error of measuring apparatus shall not exceed allowable range or 1% of resistance tolerance
Insulation resistance	Insulation resistance is 10,000M $\Omega$ Min.	Resistors shall be clamped in the trough of a 90° metallic V-block or foil method use a metal foil shall be wrapped closely around the body of the resistor. After that shall be tested at DC potential respectively specified in the above list for 60 +10/-0 secs.
Dielectric withstanding voltage	No evidence of flashover mechanical damage, arcing or insulation break down	Resistors shall be clamped in the trough of a 90° metallic V-block or foil method use a metal foil shall be wrapped closely around the body of the resistor. After that shall be tested at AC potential respectively specified in the table 1. for 60 +10/-0 secs.
Temperature coefficient	Within the temperature coefficient specified below :± 50 PPM/°C Max.	Natural resistance change per temp. degree centigrade $\frac{R_2 \cdot R_1}{R_1(t_2 \cdot t_1)} \times 10^6  (PPM/^{\circ}C)$ R1: Resistance value at room temperature (t1) R2: Resistance value at room temp. plus 100°C (t2)
Short time overload	Resistance change rate is ± (0.5% + 0.05Ω) Max. with no evidence of mechanical damage	Permanent resistance change after the application of a potential of 2.5 times RCWV for 5 seconds
Terminal strength	No evidence of mechanical damage	<b>Direct load:</b> Resistance to a 2.5 kgs direct load for 10secs. in the direction of the longitudinal axis of the terminal leads <b>Twist test :</b> Terminal leads shall be bent through 90 ° at a point of about 6mm from the body of the resistor and shall be rotated through 360° about the original axis of the bent terminal in alternating direction for a total of 3 rotations
Solderability	95% coverage Min.	The area covered with a new, smooth, clean, shiny and continuous surface free from concentrated pinholes. Test temp. of solder : $245^{\circ}C \pm 3^{\circ}C$ Dwell time in solder : $2 \sim 3$ seconds



Characteristics	Limits		Test Methods( JIS C 5201-1 )		
Soldering temp. reference	Electrical characteristics shall be satisfied. Without distinct deformation in appearance. (95 % coverage Min.)		The leads immersed into solder bath to 3.2 to 4.8 mm. from the body. Permanent resistance change shall be checked. <u>Wave soldering condition: (2 cycles Max.)</u> Pre-heat : 100 ~ 120°C, 30 ± 5 sec. Suggestion solder temp.: 235 ~ 255°C, 10 sec. (Max.) Peak temp.: 260°C <u>Hand soldering condition:</u> Hand Soldering bit temp. : 380 ± 10°C Dwell time in solder : 3 +1/-0 sec.		to 3.2 to 4.8 mm. from nge shall be checked. <u>Max.)</u> c. i°C, 10 sec. (Max.) °C
Resistance to soldering heat	Resistance change rate is $\pm(1\% + 0.05\Omega)$ Max. with no evidence of mechanical damage		Permanent resistance change when leads immersed to 3.2mm to 4.8mm from the body in $350^{\circ}C \pm 10^{\circ}C$ solder for $3 \pm 0.5$ seconds		
	Resistance change rate is $\pm(1\% + 0.05\Omega)$ Max. with no evidence of mechanical damage Resistance change rate is $\pm(1\% + 0.05\Omega)$ Max.		Resistance change after continuous 5 cycles for duty shown below:		
			Step	Temperature	Time
Temperature			1	-55°C ±3°C	30 mins
Cycling			2	Room temp.	10~15 mins
			3	+155°C ±2°C	30 mins
			4	Room temp.	10~15 mins
Vibration			55Hz, 3 p Total amp	lanes 2hrs each litude = 1.5mm	
	Resistance value	ΔR/R	Resistance change after 1,000 hours (1.5 hours "on", 0.5 hour "off") at RCWV in a humidity test chamber controlled at 40°C ±2°C and 90 to 95 % relative humidity		5
Load life in humidity	Non-Flame type	±5%			<i>NV</i> in a humidity test y
	Resistance value	ΔR/R	Permanent resistance change after		
Load life	Non-Flame type	±5%	1,000 hours operating at RCWV with duty cycle of 70°C ±2°C ambient		duty cycle of
Resistance to solvent	No deterioration of protective coatings and markings		Specimens shall be immersed in a bath of trichroethane com- pletely for 3 minutes with ultrasonic		ath of trichroethane com-
Pulse overload	Resistance change rate is toad ±(1% + 0.05Ω) Max. with no evidence of mechanical damage		Resistance change after 10,000 cycles (1 sec. "on" , 25 secs. "off" ) at 4 times RCWV		

## Dimension





# multicomp PRO

#### Painting method

Welding point, terminal and lead wire, is permissible to be exposed without the outer coated cover. The extent should be within 1/2 of the are angle.



#### Marking

#### Resistor

Resistors shall be marked with colour coding colours shall be in accordance with JIS C 0802



#### 2. Label

Label shall be marked with following items:

- 1. Type and style
- 2. Nominal resistance
- 3. Resistance tolerance
- 4. Quantity
- 5. Lot number
- 6. PPM

Description	Part Number	Description	Part Number
Axial Leaded Metal Film Resistor, 1/8W, 2.2R, ±2%	MP006658	Axial Leaded Metal Film Resistor, 1/8W, 11R, ±2%	MP006675
Axial Leaded Metal Film Resistor, 1/8W, 2.4R, ±2%	MP006659	Axial Leaded Metal Film Resistor, 1/8W, 12R, ±2%	MP006676
Axial Leaded Metal Film Resistor, 1/8W, 2.7R, ±2%	MP006660	Axial Leaded Metal Film Resistor, 1/8W, 13R, ±2%	MP006677
Axial Leaded Metal Film Resistor, 1/8W, 3R, ±2%	MP006661	Axial Leaded Metal Film Resistor, 1/8W, 15R, ±2%	MP006678
Axial Leaded Metal Film Resistor, 1/8W, 3.3R, ±2%	MP006662	Axial Leaded Metal Film Resistor, 1/8W, 16R, ±2%	MP006679
Axial Leaded Metal Film Resistor, 1/8W, 3.6R, ±2%	MP006663	Axial Leaded Metal Film Resistor, 1/8W, 18R, ±2%	MP006680
Axial Leaded Metal Film Resistor, 1/8W, 3.9R, ±2%	MP006664	Axial Leaded Metal Film Resistor, 1/8W, 20R, ±2%	MP006681
Axial Leaded Metal Film Resistor, 1/8W, 4.3R, ±2%	MP006665	Axial Leaded Metal Film Resistor, 1/8W, 22R, ±2%	MP006682
Axial Leaded Metal Film Resistor, 1/8W, 4.7R, ±2%	MP006666	Axial Leaded Metal Film Resistor, 1/8W, 24R, ±2%	MP006683
Axial Leaded Metal Film Resistor, 1/8W, 5.1R, ±2%	MP006667	Axial Leaded Metal Film Resistor, 1/8W, 27R, ±2%	MP006684
Axial Leaded Metal Film Resistor, 1/8W, 5.6R, ±2%	MP006668	Axial Leaded Metal Film Resistor, 1/8W, 30R, ±2%	MP006685
Axial Leaded Metal Film Resistor, 1/8W, 6.2R, ±2%	MP006669	Axial Leaded Metal Film Resistor, 1/8W, 33R, ±2%	MP006686
Axial Leaded Metal Film Resistor, 1/8W, 6.8R, ±2%	MP006670	Axial Leaded Metal Film Resistor, 1/8W, 36R, ±2%	MP006687
Axial Leaded Metal Film Resistor, 1/8W, 7.5R, ±2%	MP006671	Axial Leaded Metal Film Resistor, 1/8W, 39R, ±2%	MP006688
Axial Leaded Metal Film Resistor, 1/8W, 8.2R, ±2%	MP006672	Axial Leaded Metal Film Resistor, 1/8W, 43R, ±2%	MP006689
Axial Leaded Metal Film Resistor, 1/8W, 9.1R, ±2%	MP006673	Axial Leaded Metal Film Resistor, 1/8W, 47R, ±2%	MP006690
Axial Leaded Metal Film Resistor, 1/8W, 10R, ±2%	MP006674	Axial Leaded Metal Film Resistor, 1/8W, 51R, ±2%	MP006691

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



## Part Number Table

# multicomp PRO

Description	Part Number	Description	Part Number
Axial Leaded Metal Film Resistor, 1/8W, 56R, ±2%	MP006692	Axial Leaded Metal Film Resistor, 1/8W, 2.7K, ±2%	MP006732
Axial Leaded Metal Film Resistor, 1/8W, 62R, ±2%	MP006693	Axial Leaded Metal Film Resistor, 1/8W, 3K, ±2%	MP006733
Axial Leaded Metal Film Resistor, 1/8W, 68R, ±2%	MP006694	Axial Leaded Metal Film Resistor, 1/8W, 3.3K, ±2%	MP006734
Axial Leaded Metal Film Resistor, 1/8W, 75R, ±2%	MP006695	Axial Leaded Metal Film Resistor, 1/8W, 3.6K, ±2%	MP006735
Axial Leaded Metal Film Resistor, 1/8W, 82R, ±2%	MP006696	Axial Leaded Metal Film Resistor, 1/8W, 3.9K, ±2%	MP006736
Axial Leaded Metal Film Resistor, 1/8W, 91R, ±2%	MP006697	Axial Leaded Metal Film Resistor, 1/8W, 4.3K, ±2%	MP006737
Axial Leaded Metal Film Resistor, 1/8W, 100R, ±2%	MP006698	Axial Leaded Metal Film Resistor, 1/8W, 4.7K, ±2%	MP006738
Axial Leaded Metal Film Resistor, 1/8W, 110R, ±2%	MP006699	Axial Leaded Metal Film Resistor, 1/8W, 5.1K, ±2%	MP006739
Axial Leaded Metal Film Resistor, 1/8W, 120R, ±2%	MP006700	Axial Leaded Metal Film Resistor, 1/8W, 5.6K, ±2%	MP006740
Axial Leaded Metal Film Resistor, 1/8W, 130R, ±2%	MP006701	Axial Leaded Metal Film Resistor, 1/8W, 6.2K, ±2%	MP006741
Axial Leaded Metal Film Resistor, 1/8W, 150R, ±2%	MP006702	Axial Leaded Metal Film Resistor, 1/8W, 6.8K, ±2%	MP006742
Axial Leaded Metal Film Resistor, 1/8W, 160R, ±2%	MP006703	Axial Leaded Metal Film Resistor, 1/8W, 7.5K, ±2%	MP006743
Axial Leaded Metal Film Resistor, 1/8W, 180R, ±2%	MP006704	Axial Leaded Metal Film Resistor, 1/8W, 8.2K, ±2%	MP006744
Axial Leaded Metal Film Resistor, 1/8W, 200R, ±2%	MP006705	Axial Leaded Metal Film Resistor, 1/8W, 9.1K, ±2%	MP006745
Axial Leaded Metal Film Resistor, 1/8W, 220R, ±2%	MP006706	Axial Leaded Metal Film Resistor, 1/8W, 10K, ±2%	MP006746
Axial Leaded Metal Film Resistor, 1/8W, 240R, ±2%	MP006707	Axial Leaded Metal Film Resistor, 1/8W, 11K, ±2%	MP006747
Axial Leaded Metal Film Resistor, 1/8W, 270R, ±2%	MP006708	Axial Leaded Metal Film Resistor, 1/8W, 12K, ±2%	MP006748
Axial Leaded Metal Film Resistor, 1/8W, 300R, ±2%	MP006709	Axial Leaded Metal Film Resistor, 1/8W, 13K, ±2%	MP006749
Axial Leaded Metal Film Resistor, 1/8W, 330R, ±2%	MP006710	Axial Leaded Metal Film Resistor, 1/8W, 15K, ±2%	MP006750
Axial Leaded Metal Film Resistor, 1/8W, 360R, ±2%	MP006711	Axial Leaded Metal Film Resistor, 1/8W, 16K, ±2%	MP006751
Axial Leaded Metal Film Resistor, 1/8W, 390R, ±2%	MP006712	Axial Leaded Metal Film Resistor, 1/8W, 18K, ±2%	MP006752
Axial Leaded Metal Film Resistor, 1/8W, 430R, ±2%	MP006713	Axial Leaded Metal Film Resistor, 1/8W, 20K, ±2%	MP006753
Axial Leaded Metal Film Resistor, 1/8W, 470R, ±2%	MP006714	Axial Leaded Metal Film Resistor, 1/8W, 22K, ±2%	MP006754
Axial Leaded Metal Film Resistor, 1/8W, 510R, ±2%	MP006715	Axial Leaded Metal Film Resistor, 1/8W, 24K, ±2%	MP006755
Axial Leaded Metal Film Resistor, 1/8W, 560R, ±2%	MP006716	Axial Leaded Metal Film Resistor, 1/8W, 27K, ±2%	MP006756
Axial Leaded Metal Film Resistor, 1/8W, 620R, ±2%	MP006717	Axial Leaded Metal Film Resistor, 1/8W, 30K, ±2%	MP006757
Axial Leaded Metal Film Resistor, 1/8W, 680R, ±2%	MP006718	Axial Leaded Metal Film Resistor, 1/8W, 33K, ±2%	MP006758
Axial Leaded Metal Film Resistor, 1/8W, 750R, ±2%	MP006719	Axial Leaded Metal Film Resistor, 1/8W, 36K, ±2%	MP006759
Axial Leaded Metal Film Resistor, 1/8W, 820R, ±2%	MP006720	Axial Leaded Metal Film Resistor, 1/8W, 39K, ±2%	MP006760
Axial Leaded Metal Film Resistor, 1/8W, 910R, ±2%	MP006721	Axial Leaded Metal Film Resistor, 1/8W, 43K, ±2%	MP006761
Axial Leaded Metal Film Resistor, 1/8W, 1K, ±2%	MP006722	Axial Leaded Metal Film Resistor, 1/8W, 47K, ±2%	MP006762
Axial Leaded Metal Film Resistor, 1/8W, 1.1K, ±2%	MP006723	Axial Leaded Metal Film Resistor, 1/8W, 51K, ±2%	MP006763
Axial Leaded Metal Film Resistor, 1/8W, 1.2K, ±2%	MP006724	Axial Leaded Metal Film Resistor, 1/8W, 56K, ±2%	MP006764
Axial Leaded Metal Film Resistor, 1/8W, 1.3K, ±2%	MP006725	Axial Leaded Metal Film Resistor, 1/8W, 62K, ±2%	MP006765
Axial Leaded Metal Film Resistor, 1/8W, 1.4K, ±2%	MP006726	Axial Leaded Metal Film Resistor, 1/8W, 68K, ±2%	MP006766
Axial Leaded Metal Film Resistor, 1/8W, 1.6K, ±2%	MP006727	Axial Leaded Metal Film Resistor, 1/8W, 75K, ±2%	MP006767
Axial Leaded Metal Film Resistor, 1/8W, 1.8K, ±2%	MP006728	Axial Leaded Metal Film Resistor, 1/8W, 82K, ±2%	MP006768
Axial Leaded Metal Film Resistor, 1/8W, 2K, ±2%	MP006729	Axial Leaded Metal Film Resistor, 1/8W, 91K, ±2%	MP006769
Axial Leaded Metal Film Resistor, 1/8W, 2.2K, ±2%	MP006730	Axial Leaded Metal Film Resistor, 1/8W, 100K, ±2%	MP006770
Axial Leaded Metal Film Resistor, 1/8W, 2.4K, ±2%	MP006731	Axial Leaded Metal Film Resistor, 1/8W, 110K, ±2%	MP006771



# multicomp PRO

Description	Part Number	Description	Part Number
Axial Leaded Metal Film Resistor, 1/8W, 120K, ±2%	MP006772	Axial Leaded Metal Film Resistor, 1/8W, 390K, ±2%	MP006784
Axial Leaded Metal Film Resistor, 1/8W, 130K, ±2%	MP006773	Axial Leaded Metal Film Resistor, 1/8W, 430K, ±2%	MP006785
Axial Leaded Metal Film Resistor, 1/8W, 150K, ±2%	MP006774	Axial Leaded Metal Film Resistor, 1/8W, 470K, ±2%	MP006786
Axial Leaded Metal Film Resistor, 1/8W, 160K, ±2%	MP006775	Axial Leaded Metal Film Resistor, 1/8W, 510K, ±2%	MP006787
Axial Leaded Metal Film Resistor, 1/8W, 180K, ±2%	MP006776	Axial Leaded Metal Film Resistor, 1/8W, 560K, ±2%	MP006788
Axial Leaded Metal Film Resistor, 1/8W, 200K, ±2%	MP006777	Axial Leaded Metal Film Resistor, 1/8W, 620K, ±2%	MP006789
Axial Leaded Metal Film Resistor, 1/8W, 220K, ±2%	MP006778	Axial Leaded Metal Film Resistor, 1/8W, 680K, ±2%	MP006790
Axial Leaded Metal Film Resistor, 1/8W, 240K, ±2%	MP006779	Axial Leaded Metal Film Resistor, 1/8W, 750K, ±2%	MP006791
Axial Leaded Metal Film Resistor, 1/8W, 270K, ±2%	MP006780	Axial Leaded Metal Film Resistor, 1/8W, 820K, ±2%	MP006792
Axial Leaded Metal Film Resistor, 1/8W, 300K, ±2%	MP006781	Axial Leaded Metal Film Resistor, 1/8W, 910K, ±2%	MP006793
Axial Leaded Metal Film Resistor, 1/8W, 330K, ±2%	MP006782	Axial Leaded Metal Film Resistor, 1/8W, 1M, ±2%	MP006794
Axial Leaded Metal Film Resistor, 1/8W, 360K, ±2%	MP006783		

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Page <6>

