

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 215
Brand	AMF
Manufacturer Part Number	84244
DIN	787
Thread dimension	M10
Groove width	10 mm
Length excluding head	40 mm
Outer diameter	9.7 mm
Thread length	30 mm
Length of head	15 mm
Head height	6 mm
Gross Weight	0.062 kg
Product Group	260

EAN

4020772084240