

# Indoor Air Quality Meter/Datalogger


**Measures CO<sub>2</sub>, Temperature, Humidity, Dew Point and Wet Bulb**  
And automatically datalogs up to 20,000 sets or manually store/recall up to 99 sets

## Features:

- Checks for Carbon Dioxide (CO<sub>2</sub>) concentrations
- Maintenance free dual wavelength NDIR (non-dispersive infrared) CO<sub>2</sub> sensor
- Measurement ranges:
  - CO<sub>2</sub>: 0 to 6,000ppm
  - Temperature: -4 to 140°F (-20 to 60°C)
  - Humidity: 10 to 95%RH
- Continuous (20,000 sets) or manual (99 sets) datalogging
- Data hold, Max/Min with Time stamp, and Alarm
- Easy calibration in fresh air
- Complete with (6) AAA batteries, RS-232 cable, and Windows<sup>®</sup> 95/98/NT/2000/ME/XP compatible software

## Applications:

- Check air quality in schools, office buildings, greenhouses, hospitals and anywhere that high levels of carbon dioxide are generated



Included Windows<sup>®</sup> 95/98/NT/2000/ME/XP compatible software

Specifications	
CO <sub>2</sub>	0 to 6,000ppm
Resolution	1ppm
Temperature	-4 to 140°F (-20 to 60°C)
Resolution	0.1°F/°C
Humidity	10 to 95%
Resolution	1%
Datalogging	Continuous: 20,000 sets/Manual 99 sets
Dimensions	5.3 x 2.8 x 1.2" (135 x 72 x 31mm)
Weight	8.2oz (235g)

## Ordering Information:

EA80.....Indoor Air Quality Meter/Datalogger

