

Torque wrench

DREMOMETER with calibration certificate according to DIN EN ISO 6789



Application:

The tightening value is set and read from the scale by means of rotary motion with angle key integrated in the handle end.

Execution:

- Audible and perceptible release when the tightening torque is reached
- Single key, one arm, with automatic release

Advantage:

- Special design ensures faultless operation
- The measured value or set torque is not changed
- Independent of handle position



Art. no.	52248 025
Brand	GEDORE
Manufacturer Part Number	7685530
Min. torque	40 Nm
Max. torque	200 Nm
Min./max. torque	40-200 Nm
Scale value torque	5 Nm
Tip size	1/2 inch
Error limit (%)	3 %
Length	551 mm
Calibration certificate	Yes
ISO	6789
Gross Weight	2.000 kg
Product Group	556

EAN

4002805857311