

## Pt100 - Surface sensor

waterproof design



### Application:

The robust, waterproof surface sensor enables a particularly precise measurement of the surface temperature.

### Execution:

- Sensor type: Pt100
- Measuring range: -50 to +400°C
- Accuracy: Class B in accordance with EN 60751
- Response time: 40 s
- Length/diameter of probe/sensor tube: 120 mm/5 mm
- Length/diameter of probe/sensor tube tip: 55 mm/9 mm
- Product/housing material: ABS/TPE/PUR
- EN 13485 and HACCP-compliant



<b>Art. no.</b>	<b>46108 060</b>
<b>Brand</b>	TESTO
<b>Manufacturer Part Number</b>	0609 1973
<b>Sensor type</b>	Pt100
<b>Probe type</b>	Surface probe
<b>Min./max. temperature measuring range</b>	-50 to 400 °C
<b>Accuracy temperature</b>	Class B according to EN 60584-2
<b>Response time sensor</b>	40 s
<b>Diameter probe tube</b>	5 mm
<b>Diameter sensor tube tip</b>	9 mm
<b>Length sensor tube</b>	120 mm
<b>Length sensor tube tip</b>	55 mm
<b>Cable length</b>	1.3 m
<b>IP protection class</b>	IP 65
<b>EN standard</b>	13485
<b>Material of housing</b>	ABS/TPE/PUR
<b>Gross Weight</b>	0.150 kg
<b>Product Group</b>	4CF

### EAN

4029547002816