



# MSR

## MSR 400 1CT/4

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

### Product data


GeniPubl	
Cap-Base	GX9.5 [ GX9.5]
Operating Position	UNIVERSAL [ Any or Universal (U)]
Main Application	Studio/Disco
Life to 50% Failures (Nom)	1000 h
System Description	Cold Strike
LittPubl	
Color Code	- [ Not Specified]
Luminous Flux (Min)	28500 lm
Luminous Flux (Nom)	32000 lm
Chromaticity Coordinate X (Nom)	325
Chromaticity Coordinate Y (Nom)	320
Correlated Color Temperature (Nom)	5900 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color Rendering Index (Nom)	95
ElecPubl	
Power (Nom)	400 W
Lamp Current (Nom)	6.9 A

Ignition Supply Voltage (Min)	207 V
CntrPubl	
Dimmable	No
MechPubl	
Cap-Base Information	-
LDRPubl	
Bulb Temperature (Max)	700 °C
Pinch Temperature (Max)	350 °C
ProductPubl	
Full product code	871869641600600
Order product name	MSR 400 1CT/4
EAN/UPC - Product	8718696416006
Order code	928077905115
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928077905115

Net Weight (Piece)	44.000 g
--------------------	----------

Warnings and Safety

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 400	23 mm	6.0	61 mm	63 mm	62	112 mm	36 mm	35	34 mm
1CT/4		mm			mm			mm	

MSR 400

Photometric data

