

15EBS1 ✓ ACTIVE

Corcom | Corcom EEB

TE Internal #: 1-6609005-5

Corcom EEB, Multi-Function Inlet Filters, Power Line, Right Angle,
Leakage Current (Max) (120VAC, 60Hz) 220 μ A

[View on TE.com >](#)



EMI Filters > Multi-Function Inlet Filters > CORCOM EEB SERIES IEC FILTERED INLETS



Filter Type: **Power Line**

Mount Angle: **Right Angle**

Leakage Current (Max) (120VAC, 60Hz): **220 μ A**

Leakage Current (Max) (250VAC, 50Hz): **380 μ A**

Filter Current Rating: **15 A**

[All CORCOM EEB SERIES IEC FILTERED INLETS \(18\)](#)

Features

Product Type Features

Ground Choke Option	No
Ground Option	None
Filter Type	Power Line
Filter Input Termination Type	IEC
Filter Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	220 μ A
Leakage Current (Max) (250VAC, 50Hz)	380 μ A
Filter Current Rating	15 A
Voltage Rating (Max)	250 VAC

Mechanical Attachment

Mount Angle	Right Angle
Filter Mount Style	Snap-In

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | **Corcom EEB**



Multi-Function Inlet Filters(18)

Customers Also Bought



TE Part #1658676-1
D-Sub Crimp: Plug, Signal, 26 Posn,
Pin Size 22, Shell Size 2



TE Part #1658655-1
D-Sub Crimp: Plug, Signal, 9 Posn, Pin
Size 20, Shell Size 1



TE Part #2-320619-1
PIDG RING TONGUE TERMINALS



TE Part #103653-4
05 MTE SHRD PIN HSG SR LATCH




TE Part #134019-1
PIDG R 12 IR 5MM



TE Part #1658528-2
636-1041LF FEM SOCKET, LEAD FREE



TE Part #1658656-1
D-Sub Crimp Recept Signal 15 Posn,
Socket Size 20, Shell Size 2



TE Part #1051815-1
2031 8128 92



TE Part #YACT20JF35SNV00100
SQUARE FLANGE RECEPTACLE

Documents

Product Drawings

15EBS1=F7900N S0

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-6609005-5_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-6609005-5_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-6609005-5_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE](#)

English

[Corcom Combined Selector Charts](#)

English