

## PWLN clamp holder with internal cooling, negative

For copy and longitudinal face turning using WN indexable inserts

**ATORN**<sup>®</sup>

### Application

For copy, longitudinal and face turning with WN indexable insert, 80°.

### Version

- precision-made steel carrier with high-performance cooling system, nickel-plated, hardened, adjustable clamping system, type W, attack angle 93°, tip angle 80°, clearance angle 0°

### Advantage

- high-performance cooling channel system with three outlets ensures an extremely long service life and reliable working
- Triple-edge geometry lowers cost per cut
- Negative geometry of the body ensures good stability and force absorption at large cutting depths
- Broad range of use: suitable for both finishing and roughing operations
- adjustable clamp minimises vibrations and ensures good power transmission



<b>Art. no.</b>	<b>17839 715</b>
<b>ISO name</b>	PWLN R/L 2020 K08 IK G1/8
<b>Shaft height</b>	20 mm
<b>Shank width</b>	20 mm
<b>Length</b>	150 mm
<b>Length of head</b>	34 mm
<b>Programming size</b>	32 mm
<b>Suitable for indexable inserts</b>	WN.. 0804..
<b>Tool design</b>	Right
<b>DIN</b>	4983

### EAN-Code

4050293566086