

Micrometer

with replaceable inserts

Mitutoyo

Application:

For measuring e.g. Screw thread

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Friction coupling for consistent, repeatable measuring force

Delivery:

Includes box, setting standard (60°), adjustment wrench



Art. no.	32016 697
Brand	MITUTOYO
Manufacturer Part Number	126-134
Min./max. length measuring range	220-250 mm
Vernier scale	0.01 mm
Measuring surface diameter	6.3 mm
Measuring spindle increments	0.5 mm
Bracket depth	144 mm
Spindle clamping	Yes
Error limit	7 µm
Display	Nonius
Min./max. measurement force	5-10 N
DIN	863
Calibration Group	D
Gross Weight	2.280 kg
Product Group	3MA

EAN

4946368015774