



**Part no.: 50110569**  
**TKS 20x75**  
**Reflector**

Figure can vary

## Contents

- Technical data
- Dimensioned drawings

Part no.: 50110569 – TKS 20x75 – Reflector

## Technical data

<b>Mechanical data</b>	
Design	Rectangular
Mounting dimension, width	20 mm
Reflection surface width	15 mm
Mounting dimension, height	76 mm
Reflection surface height	70 mm
Mounting dimension, thickness	11 mm
Triple reflector size	2.6 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Type of fastening	M4 x 19 mm threaded pin

<b>Environmental data</b>	
Ambient temperature, operation	-40 ... 65 °C

<b>Certifications</b>	
Degree of protection	IP 67

<b>Classification</b>	
Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

## Dimensioned drawings

All dimensions in millimeters

