

		Conditions		Diagrams	
<b>cell type:</b>		NiMH			
<b>cell size:</b>		E-block			
<b>nominal voltage:</b>	8.4	V			
<b>max. charge voltage:</b>	10.5	V			
		at standard charge (0.1C / 20°C)			
<b>capacity</b>					
nominal:	300	mAh			
minimum:	270	mAh			
		discharge at 1C			
		7.0V end discharge voltage			
		ta: 20°C			
<b>max. continuous discharge current:</b>	400	mA			
		ta: 0...45°C			
<b>charge</b>					
standard charge:	30	mA			
quick charge:	85	mA			
fast charge:	300	mA			
		1.1hrs			
<b>recommended charge termination control parameters:</b>	15...35	mV			
	120	%			
		- delta V of nominal input by timer cut off			
<b>trickle charge current:</b>	2...15	mA		(recommended)	
<b>continuous overcharge:</b> (less than 1 year)	≤ 30	mA		no conspicuous deformation no leakage	
<b>internal resistance:</b> (impedance)	≤ 0.8	Ω		at 1KHz battery fully charged	
<b>life expectancy:</b>	≥ 500	cycles		acc. IEC standard	
<b>self discharge</b>					
charge retention:	≥ 85	%		after 6 months storage	
(at ≤ 20°C ambient)	≥ 80	%		after 12 months storage	
<b>initial capacity:</b>	≥ 200	mAh		within 30 days after delivery discharge at 0.2C	
<b>ambient temperature range:</b>	0...45	°C		standard charge	
	10...40	°C		fast charge	
	0...45	°C		discharge (≥1C)	
	- 20...65	°C		discharge (<1C)	
	- 20...50	°C		storage (≤3months)	
	- 20...40	°C		storage (≤6months)	
	- 20...30	°C		storage (≤24months)	
<b>QCT1:</b>	20/260/750				
<b>QCT2:</b>	30/240/800				
<b>mechanical specifications</b>					
cell dimensions (incl. label)					
Length L1:	26.5 - 2.0	mm			
Length L2:	17.5 - 2.0	mm			
Length L3:	12.7 ± 0.25	mm			
height h1:	48.5 - 1.0	mm			
weight:	45 ± 4	g			
blister card dimensions:	123 x 85	mm			
blister card weight (incl. battery):	53	g			

	<b>ANSMANN Specifications for model:</b>	<b>9V-E-block 300mAh low self discharge</b> <b>1pc blister package</b>
	data sheet no. / part no.	5035453
	supplier no.	701364
	author / date	Gramlich / 05.03.2012

Manufacturer reserves the right to alter or amend the design, model and specification without prior notice