

WASP POWDER

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Date of issue: 16/05/2019

Version: 3.0

Rentokil

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : WASP POWDER
Type of product : Biocide
Registration No : HSE 10556, PCS 99502
Product group : Product

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Intended for general public
Main use category : Consumer use
Use of the substance/mixture : An insecticidal powder for amateur use against wasps in domestic and commercial premises.
Use of the substance/mixture : Insecticide

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Supplier

Rentokil Initial Supplies
Liverpool
L33 7SR
UK

Product advice line: +44 (0)151 548 5050

Email: sds@rentokil.com

National Contact

For UK:

Rentokil Initial Supplies
Liverpool
L33 7SR
UK

For Ireland:

Rentokil Initial,
Hazel House,
Millennium Park,
Naas, Co Kildare,
Ireland

Tel: +353 (0)45 850 799

1.4. Emergency telephone number

Emergency number : +44 (0)1342 833022

Country	Organisation/Company	Address	Emergency number	Comment
Ireland	National Poisons Information Centre Beaumont Hospital	PO Box 1297 Beaumont Road 9 Dublin	+353 1 809 2566 (Healthcare professionals-24/7) +353 1 809 2166 (public, 8am - 10pm, 7/7)	
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Hazardous to the aquatic environment — Chronic Hazard, Category 2 H411

Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

WASP POWDER

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS09

Signal word (CLP) :

-

Hazard statements (CLP) :

H411 - Toxic to aquatic life with long lasting effects.

Precautionary statements (CLP) :

P101 - If medical advice is needed, have product container or label at hand.
P102 - Keep out of reach of children.
P260 - Do not breathe dust.
P273 - Avoid release to the environment.
P391 - Collect spillage.
P501 - Dispose of container, contents to normal household waste. However if used in a place of work any product and empty container must be disposed of as controlled waste..

EUH-statements :

EUH208 - Contains Chrysanthemum cinerariaefolium, extract from open and mature flowers of Tanacetum cinerariifolium obtained with hydrocarbon solvents. May produce an allergic reaction.

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Nepheline syenite substance with national workplace exposure limit(s) (GB)	(CAS-No.) 37244-96-5 (EC-No.) 270-666-7	>= 75	Not classified
Piperonyl Butoxide (PBO)	(CAS-No.) 51-03-6 (EC-No.) 200-076-7	0.1 - 0.5	Aquatic Acute 1, H400 Aquatic Chronic 1, H410
Chrysanthemum cinerariaefolium, extract from open and mature flowers of Tanacetum cinerariifolium obtained with hydrocarbon solvents	(CAS-No.) 89997-63-7 (EC-No.) 232-319-8	0.11	Acute Tox. 4 (Oral), H302 Acute Tox. 4 (Dermal), H312 Acute Tox. 4 (Inhalation), H332 Skin Sens. 1, H317 Aquatic Acute 1, H400 (M=100) Aquatic Chronic 1, H410 (M=100)
Butylated Hydroxytoluene substance with national workplace exposure limit(s) (GB, IE)	(CAS-No.) 128-37-0 (EC-No.) 204-881-4	0.001 - 0.1	Aquatic Acute 1, H400 Aquatic Chronic 1, H410

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing. Allow affected person to breathe fresh air. Allow the victim to rest.
First-aid measures after skin contact	: Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse.
First-aid measures after eye contact	: Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects : If you feel unwell, seek medical advice (show the label where possible). Not expected to present a significant hazard under anticipated conditions of normal use.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

WASP POWDER

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.
Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

No additional information available

5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.
Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.
Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if product enters sewers or public waters. Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : On land, sweep or shovel into suitable containers. Minimise generation of dust.

6.4. Reference to other sections

Please also see sections 8 and 13 for further information.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work.
Hygiene measures : Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep only in the original container in a cool well ventilated place. Keep away from food, drink and animal feeding stuffs. When not in use, keep containers tightly closed. Keep away from children.
Incompatible products : Strong bases. Strong acids.
Incompatible materials : Sources of ignition. Direct sunlight.

7.3. Specific end use(s)

Insecticide.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Chrysanthemum cinerariaefolium, extract from open and mature flowers of Tanacetum cinerariifolium obtained with hydrocarbon solvents (89997-63-7)		
EU	Local name	Pyrethrum (purified of sensitising lactones)
EU	IOELV TWA (mg/m ³)	1 mg/m ³
Ireland	Local name	Pyrethrins (ISO)
Ireland	OEL (8 hours ref) (mg/m ³)	1 mg/m ³
Ireland	Notes (IE)	IOELV
United Kingdom	Local name	Pyrethrum
United Kingdom	WEL TWA (mg/m ³)	1 mg/m ³ purified of sensitising lactones
Butylated Hydroxytoluene (128-37-0)		
Ireland	Local name	2,6-Ditertiary-butyl-para- cresol
Ireland	OEL (8 hours ref) (mg/m ³)	10 mg/m ³
United Kingdom	Local name	2,6-Di-tert-butyl-p-cresol
United Kingdom	WEL TWA (mg/m ³)	10 mg/m ³

WASP POWDER

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Nepheline syenite (37244-96-5)

United Kingdom Dust, inorganic (respirable dust): 4 mg/m³

8.2. Exposure controls

Personal protective equipment:

Avoid all unnecessary exposure.

Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Solid
Appearance	: Powder.
Colour	: White to off-white.
Odour	: Odourless.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 0.45
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available.
Oxidising properties	: No data available.
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is stable at normal handling and storage conditions.

10.2. Chemical stability

The product is stable at normal handling and storage conditions.

10.3. Possibility of hazardous reactions

None expected under normal conditions of handling and use.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

Fume. Carbon monoxide. Carbon dioxide.

WASP POWDER

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity : Not classified

Chrysanthemum cinerariaefolium, extract from open and mature flowers of Tanacetum cinerariifolium obtained with hydrocarbon solvents (89997-63-7)

LD50 oral rat	2370 mg/kg male
LD50 oral	1030 mg/kg female
LD50 dermal rat	> 1500 mg/kg
LD50 dermal rabbit	5000 mg/kg
LC50 inhalation rat (mg/l)	3.4 mg/l/4h

Butylated Hydroxytoluene (128-37-0)

LD50 oral rat	> 2930 mg/kg
---------------	--------------

Piperonyl Butoxide (PBO) (51-03-6)

LD50 oral rat	4570 mg/kg bodyweight male
LD50 oral	7220 mg/kg bodyweight female
LD50 dermal rabbit	> 2000 mg/kg bodyweight
LC50 inhalation rat (Dust/Mist - mg/l/4h)	> 5.9 mg/l/4h

Skin corrosion/irritation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Serious eye damage/irritation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Respiratory or skin sensitisation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Germ cell mutagenicity	: Not classified
	Based on available data, the classification criteria are not met
Carcinogenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Reproductive toxicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
STOT-single exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met
STOT-repeated exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Aspiration hazard	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Potential adverse human health effects and symptoms	: Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

12.1. Toxicity

Ecology - water : Toxic to aquatic life with long lasting effects.

Chrysanthemum cinerariaefolium, extract from open and mature flowers of Tanacetum cinerariifolium obtained with hydrocarbon solvents (89997-63-7)

LC50 fish 1	5.2 µg/l Rainbow trout
EC50 Daphnia 1	12 µg/l
EC50 other aquatic organisms 1	1.27 mg/l Algae

Butylated Hydroxytoluene (128-37-0)

LC50 fish 1	> 0.57 mg/l
EC50 Daphnia 1	0.61 mg/l

Piperonyl Butoxide (PBO) (51-03-6)

LC50 fish 1	3.94 mg/l
EC50 Daphnia 1	0.51 mg/l

WASP POWDER

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

12.2. Persistence and degradability

WASP POWDER

Persistence and degradability	May cause long-term adverse effects in the environment.
-------------------------------	---

12.3. Bioaccumulative potential

WASP POWDER

Bioaccumulative potential	Not established.
---------------------------	------------------

Piperonyl Butoxide (PBO) (51-03-6)

BCF fish 1	91 (260 - 380)
------------	----------------

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Additional information : Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : This product is for amateur use and can be disposed of as normal household waste. However, if used in a place of work, any product and empty container must be disposed of as controlled waste.

Ecology - waste materials : Avoid release to the environment.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

14.1. UN number

UN-No. (ADR)	: 3077
UN-No. (IMDG)	: 3077
UN-No. (IATA)	: 3077
UN-No. (ADN)	: 3077
UN-No. (RID)	: 3077


14.2. UN proper shipping name

Proper Shipping Name (ADR)	: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S.
Proper Shipping Name (IMDG)	: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S.
Proper Shipping Name (IATA)	: Environmentally Hazardous Substance, Solid, N.O.S
Proper Shipping Name (ADN)	: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S.
Proper Shipping Name (RID)	: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S.
Transport document description (ADR)	: UN 3077 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Contains: Pyrethrins including Cinerins), 9, III, (-)
Transport document description (IMDG)	: UN 3077 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Contains: Pyrethrins including Cinerins), 9, III, MARINE POLLUTANT
Transport document description (IATA)	: UN 3077 Environmentally Hazardous Substance, Solid, N.O.S (Contains: Pyrethrins including Cinerins), 9, III
Transport document description (ADN)	: UN 3077 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Contains: Pyrethrins including Cinerins), 9, III
Transport document description (RID)	: UN 3077 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Contains: Pyrethrins including Cinerins), 9, III

14.3. Transport hazard class(es)

ADR

Transport hazard class(es) (ADR)	: 9
Danger labels (ADR)	: 9,




WASP POWDER

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830


IMDG

Transport hazard class(es) (IMDG) : 9
Danger labels (IMDG) : 9,




IATA

Transport hazard class(es) (IATA) : 9
Hazard labels (IATA) : 9,




ADN

Transport hazard class(es) (ADN) : 9
Danger labels (ADN) : 9,



RID

Transport hazard class(es) (RID) : 9
Danger labels (RID) : 9,



14.4. Packing group

Packing group (ADR) : III
Packing group (IMDG) : III
Packing group (IATA) : III
Packing group (ADN) : III
Packing group (RID) : III

14.5. Environmental hazards

Dangerous for the environment : Yes
Marine pollutant : Yes
Other information : No supplementary information available

14.6. Special precautions for user

- Overland transport


Classification code (ADR) : M7
Special provisions (ADR) : 274, 335, 375, 601
Limited quantities (ADR) : 5kg
Excepted quantities (ADR) : E1
Packing instructions (ADR) : P002, IBC08, LP02, R001
Special packing provisions (ADR) : PP12, B3
Mixed packing provisions (ADR) : MP10

WASP POWDER

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Portable tank and bulk container instructions (ADR)	: T1, BK1, BK2, BK3
Portable tank and bulk container special provisions (ADR)	: TP33
Tank code (ADR)	: SGAV, LGBV
Vehicle for tank carriage	: AT
Transport category (ADR)	: 3
Special provisions for carriage - Packages (ADR)	: V13
Special provisions for carriage - Bulk (ADR)	: VC1, VC2
Special provisions for carriage - Loading, unloading and handling (ADR)	: CV13
Hazard identification number (Kemler No.)	: 90
Orange plates	:



Tunnel restriction code (ADR)	: -
EAC code	: ZZ

- Transport by sea

Special provisions (IMDG)	: 274, 335, 966, 967, 969
Packing instructions (IMDG)	: P002, LP02
Special packing provisions (IMDG)	: PP12
IBC packing instructions (IMDG)	: IBC08
IBC special provisions (IMDG)	: B3
Tank instructions (IMDG)	: T1, BK1, BK2, BK3
Tank special provisions (IMDG)	: TP33
EmS-No. (Fire)	: F-A
EmS-No. (Spillage)	: S-F
Stowage category (IMDG)	: A
Stowage and handling (IMDG)	: SW23

- Air transport

PCA Excepted quantities (IATA)	: E1
PCA Limited quantities (IATA)	: Y956
PCA limited quantity max net quantity (IATA)	: 30kgG
PCA packing instructions (IATA)	: 956
PCA max net quantity (IATA)	: 400kg
CAO packing instructions (IATA)	: 956
CAO max net quantity (IATA)	: 400kg
Special provisions (IATA)	: A97, A158, A179, A197
ERG code (IATA)	: 9L

- Inland waterway transport

Classification code (ADN)	: M7
Special provisions (ADN)	: 274, 335, 375, 601
Limited quantities (ADN)	: 5 kg
Excepted quantities (ADN)	: E1
Equipment required (ADN)	: PP, A
Number of blue cones/lights (ADN)	: 0
Additional requirements/Remarks (ADN)	: * Only in the molten state. ** For carriage in bulk see also 7.1.4.1. *** Only in the case of transport in bulk.

- Rail transport

Classification code (RID)	: M7
Special provisions (RID)	: 274, 335, 375, 601
Excepted quantities (RID)	: E1
Packing instructions (RID)	: P002, IBC08, LP02, R001
Special packing provisions (RID)	: PP12, B3
Mixed packing provisions (RID)	: MP10

WASP POWDER

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Portable tank and bulk container instructions (RID)	: T1, BK1, BK2, BK3
Portable tank and bulk container special provisions (RID)	: TP33
Tank codes for RID tanks (RID)	: SGAV, LGBV
Transport category (RID)	: 3
Special provisions for carriage – Packages (RID)	: W13
Special provisions for carriage – Bulk (RID)	: VC1, VC2
Special provisions for carriage - Loading, unloading and handling (RID)	: CW13, CW31
Colis express (express parcels) (RID)	: CE11
Hazard identification number (RID)	: 90

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Indication of changes:

	Date of issue	Modified	
3		Modified	

Abbreviations and acronyms:

REACH	Registration, Evaluation, Authorisation and Restriction of Chemicals Regulation (EC) No 1907/2006
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
IMDG	International Maritime Dangerous Goods
IATA	International Air Transport Association
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
LD50	Median lethal dose
EC50	Median effective concentration
PBT	Persistent Bioaccumulative Toxic
CLP	Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Full text of H- and EUH-statements:

Acute Tox. 4 (Dermal)	Acute toxicity (dermal), Category 4
Acute Tox. 4 (Inhalation)	Acute toxicity (inhal.), Category 4
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Aquatic Chronic 1	Hazardous to the aquatic environment — Chronic Hazard, Category 1
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Skin Sens. 1	Skin sensitisation, Category 1
H302	Harmful if swallowed.
H312	Harmful in contact with skin.
H317	May cause an allergic skin reaction.

WASP POWDER

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

H332	Harmful if inhaled.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.
EUH208	Contains Chrysanthemum cinerariaefolium, extract from open and mature flowers of Tanacetum cinerariifolium obtained with hydrocarbon solvents. May produce an allergic reaction.

Classification and procedure used to derive the classification for mixtures according to Regulation (EC) 1272/2008 [CLP]:

Aquatic Chronic 2	H411	Calculation method
-------------------	------	--------------------

RI - SDS EU (REACH Annex II) CLP

Before using any product, ensure that you read and understand its label.

The information contained in this safety data sheet is, to the best of our knowledge and belief, accurate and reliable at the time of publication. The information relates only to the specific material designated in this safety data sheet and may not be valid for such material if it is used in combination with any other material(s) or any other use than that specified herein. Neither Rentokil Initial plc nor any of its subsidiaries accepts any liability for the use of this product for any other purpose than that described in this safety data sheet. This does not affect your statutory rights. It is the user's responsibility to satisfy him/herself as to the suitability in completeness of such information for his/her own particular use.

Copyright © (2019) Rentokil Initial plc, Rentokil Initial Power Centre, Unit A1 & A2 Link 10, Napier Way, Crawley, RH10 9RA. United Kingdom.

Telephone: +44 (0) 1342 833022