

Multilayer Ceramic Capacitors **multicomp**PRO

**RoHS
Compliant**



Features

- A wide selection of sizes is available (0402 to 1812)
- High capacitance in given case size
- Capacitor with lead-free termination (pure Tin)


Description

MLCC consists of a conducting material and electrodes. To manufacture a chip-type SMT and achieve miniaturization, high density and high efficiency, ceramic condensers are used.

MLCC is made by NP0, X7R and Y5V dielectric material and which provides product with high electrical precision, stability and reliability

Application

- General digital circuit.
- Power supply bypass capacitors.
- Consumer electronics.
- Telecommunication.



External Dimensions

Size Inches (mm)	L (mm)	W (mm)	T (mm) / Symbol		Remark	M _B (mm)
0603 (1608)	1.6 ±0.1	0.8 ±0.1	0.8 ±0.07	S		0.4 ±0.15
	1.6 +0.15 / -0.1	0.8 +0.15 / -0.1	0.8 +0.15 / -0.1	X		
0805 (2012)	2 ±0.15	1.25 ±0.1	0.6 ±0.1	A		0.5 ±0.2
			0.8 ±0.1	B		
			1.25 ±0.1	D	#	
1206 (3216)	3.2 ±0.15	1.6 ±0.15	0.8 ±0.1	B		0.6 ±0.2
			0.95 ±0.1	C		
			1.15 ±0.15	J	#	
			1.25 ±0.1	D		
	3.2 ±0.2	1.6 ±0.2	1.6 ±0.2	G		
	3.2 +0.3 / -0.1	1.6 +0.3 / -0.1	1.6 +0.3 / -0.1	P		

Reflow soldering only is recommended.

General Electrical Data

Dielectric	NPO	X7R	Y5V
Size	0603, 0805, 1206		
Capacitance Range*	0.5pF to 0.039µF	100pF to 1µF	10nF to 680nF
Capacitance Tolerance**	Cap ≤ 5pF: B (±0.1pF), C (±0.25pF) 5pF < Cap < 10pF: C (±0.25pF), D (±0.5pF) Cap ≥ 10pF: F (±1%), G (±2%), J (±5%), K (±10%)	J (±5%), K (±10%), M (±20%)	M (±20%), Z (-20% / +80%)

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicompPRO

Multilayer Ceramic Capacitors **multicomp**PRO

Dielectric	NPO	X7R	Y5V
Rated Voltage (WVDC)	16V, 25V, 50V, 100V	10V, 16V, 25V, 50V, 100V	
Tan δ^*	Cap < 30pF: Q \geq 400+20C Cap \geq 30pF: Q \geq 1,000	Note 1	
Insulation resistance at Ur	$\geq 10\Omega$ or $R \times C \geq 500\Omega \times F$ whichever is less		
Operating Temperature	-55°C to +125°C		-25°C to +85°C
Capacitance Characteristic	± 30 ppm	$\pm 15\%$	+30% / -80%
Termination	Ni / Sn (lead-free termination)		

* Measured at the condition of 30 to 70% related humidity

NPO : Apply 1 ± 0.2 Vrms, 1MHz $\pm 10\%$ for Cap \leq 1,000pF and 1 ± 0.2 Vrms, 1kHz $\pm 10\%$ for Cap > 1,000pF, 25°C at ambient temperature

X7R : Apply 1 ± 0.2 Vrms, 1kHz $\pm 10\%$, at 25°C ambient temperature

Y5V : Apply 1 ± 0.2 Vrms, 1kHz $\pm 10\%$, at 20°C ambient temperature

** Preconditioning for Class II MLCC: Perform a heat treatment at 150 $\pm 10^\circ$ C for 1 hour, then leave in ambient condition for 24 ± 2 hours before measurement.

Note 1:

X7R

Rated vol.	D.F.	Exception of D.F.	
$\geq 50V$	$\leq 2.5\%$	$\leq 3\%$	0603 $\geq 0.047\mu F$; 0805 $\geq 0.18\mu F$, 1206 $\geq 0.47\mu F$
25V	$\leq 3.5\%$	$\leq 5\%$	0805 $\geq 1\mu F$; 1210 $\geq 10\mu F$
		$\leq 7\%$	0603 $\geq 0.33\mu F$
		10%	0402 $\geq 0.1\mu F$; 0603 $\geq 0.68\mu F$
16V	$\leq 3.5\%$	$\leq 5\%$	0402 $\geq 0.033\mu F$; 0603 $\geq 0.15\mu F$; 0805 $\geq 0.68\mu F$; 1206 $\geq 2.2\mu F$
		$\leq 10\%$	1210 $\geq 22\mu F$; 0603 $\geq 0.68\mu F$
10V	$\leq 5\%$	$\leq 10\%$	0603 $\geq 0.33\mu F$; 0805 $\geq 2.2\mu F$

Y5V

Rated vol.	D.F.	Exception of D.F.	
$\geq 50V$	$\leq 5\%$	7%	0603 $\geq 0.1\mu F$; 0805 $\geq 0.47\mu F$
25V	$\leq 5\%$	$\leq 7\%$	0402 $\geq 0.047\mu F$; 0603 $\geq 0.1\mu F$; 0805 $\geq 0.33\mu F$; 1206 $\geq 1\mu F$
		$\leq 9\%$	0402 $\geq 0.068\mu F$; 0603 $\geq 0.47\mu F$
16V (C < 1 μF)	$\leq 7\%$	$\leq 9\%$	0402 $\geq 0.068\mu F$; 0603 $\geq 0.68\mu F$
16V (C $\geq 1\mu F$)	$\leq 9\%$	$\leq 12.5\%$	0805 $\geq 3.3\mu F$; 1206 $\geq 10\mu F$; 1210 $\geq 22\mu F$; 1812 $\geq 47\mu F$
10V	$\leq 12.5\%$		0402 $\geq 0.47\mu F$

Capacitance Range (0603)

Dielectric	NPO			X7R			Y5V		
Size	0603								
Rated Voltage (V DC)	16 (V)	25 (V)	50 (V)	16 (V)	25 (V)	50 (V)	16 (V)	25 (V)	50 (V)
22pF (220)	S	S	S	-	-	-	-	-	-
100pF (101)	S	S	S	S	S	S	-	-	-

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicompPRO

Multilayer Ceramic Capacitors **multicomp**PRO

Dielectric	NP0			X7R			Y5V		
Size	0603								
Rated Voltage (V DC)	16 (V)	25 (V)	50 (V)	16 (V)	25 (V)	50 (V)	16 (V)	25 (V)	50 (V)
220pF (221)	S	S	S	S	S	S	-	-	-
1,000pF (102)	S	S	S	S	S	S	-	-	-
0.1μF (104)	-	-	-	S	S	S	S	S	S
220pF (221)	S	S	S	S	S	S	-	-	-
470pF (471)	S	S	S	S	S	S	-	-	-
0.01μF (103)	-	-	-	-	-	-	S	S	S

1. The letter in cell is expressed the symbol of product thickness.

Capacitance Range (0805)

Dielectric	NP0			X7R			Y5V		
Size	0805								
Rated Voltage (V DC)	16 (V)	50 (V)	100 (V)	16 (V)	50 (V)	100 (V)	16 (V)	50 (V)	100 (V)
1,000pF (102)	B	B	B	B	B	B	-	-	-
2,200pF (222)	B	B	B	B	B	B	-	-	-
0.22μF (224)	-	-	-	D	D	-	-	-	-
0.33μF (334)	-	-	-	D	D	-	-	-	-
0.47μF (474)	-	-	-	D	D	-	-	-	-
100pF	-	-	-	B	B	B	-	-	-
220pF	A	A	A	B	B	B	-	-	-
470pF	-	-	-	B	B	B	-	-	-
0.22μF (224)	-	-	-	D	D	-	-	-	-
0.33μF (334)	-	-	-	D	D	-	B	B	-
0.47μF (474)	-	-	-	D	D	-	B	B	-
0.01μF (103)	D	-	-	B	B	B	A	A	B
0.022μF (223)	-	-	-	B	B	B	A	A	B
0.047μF (473)	-	-	-	B	B	D	-	-	-
0.1μF (104)	-	-	-	B	B	D	-	-	-

1. The letter in cell is expressed the symbol of product thickness.

Capacitance Range (1206)

Dielectric	NP0		X7R		Y5V	
Size	1206					
Rated Voltage (V DC)	25 (V)	50 (V)	25 (V)	50 (V)	25 (V)	50 (V)
0.33μF	-	-	C	D	B	B
0.47μF	-	-	J	P	B	B

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicompPRO



Multilayer Ceramic Capacitors **multicomp**PRO

Dielectric	NP0		X7R		Y5V	
Size	1206					
Rated Voltage (V DC)	25 (V)	50 (V)	25 (V)	50 (V)	25 (V)	50 (V)
10nF	-	-	-	-	-	-
100nF	-	-	-	-	-	-


1. The letter in cell is expressed the symbol of product thickness.

Recommended soldering conditions

The lead-free termination MLCCs are not only to be used on SMT against lead-free solder paste, but also suitable against leadcontaining solder paste. If the optimized solder joint is requested, increasing soldering time, temperature and concentration of N2 within oven are recommended.



Part Number Explanation



Rated Voltage : Two significant digits followed by no. of zeros and R is in place of decimal point)
A = 100V, B = 16V, T = 25V and U = 50V

Size : 0603 inches (1608 mm), 0805 inches (2012 mm) and 1206 inches (3216 mm)

Dielectric : C = NP0 (C0G), R = X7R and F = Y5V

Capacitance : Two significant digits followed by number of zeros and R is in place of decimal point
eg: 102 = $10 \times 10^2 = 1,000$ pF

Tolerance : B = ± 0.1 pF, C = ± 0.25 pF, D = ± 0.5 pF, F = $\pm 1\%$, G = $+2\%$ and J = $+5\%$

Termination : C = Cu / Ni / Sn

Packaging : T = 7 inches reeled

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicompPRO