




▷ ISO 5749, DIN ISO 5749, NF E 73-105

- Edges designed for clean cut in copper wire.
- High-frequency hardened cutting edges for durable cut accuracy.
- Snipe nose for manoeuvrability in control cabinets or cutting cable loom ties.
- 4 options
- CPE Chrome finish, ergonomic grips, return spring.
- TE Varnish finish, ergonomic grips, return spring.
- G Varnish finish, PVC grips.
- VE Varnish finish, return spring, 1000V insulated grips for electrical safety to EN 60900 and , for working on or near live components.




Zoom

Zoom



Zoom

▼ Dessins Techniques



Zoom

▼ Données Techniques

|  | ∅ max mm Cu | B1 mm | B2 mm | L mm | A mm | C mm |  g |
|---|----------------|----------|----------|---------|---------|---------|--|
| 391.16CPE | 3,5 | 21 | 13,5 | 165 | 19 | 10 | 190 |
| 391.16TE | 3,5 | 21 | 13,5 | 165 | 19 | 10 | 190 |
| 391.16G | 3,5 | 21 | 13,5 | 160 | 19 | 10 | 160 |
| 391.16VE | 3,5 | 21 | 13,5 | 165 | 19 | 10 | 200 |