

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015247100](#)
Status: **Active**
Overview: [Mini-Fit Products](#)
Description: Mini-Fit BMI Receptacle Header, 4.20mm Pitch, Dual Row, Vertical, with Snap-In Plastic Pegs, Post 2.54µm Tin (Sn), UL 94V-2, 10 Circuits

Documents:

3D Model	Packaging Specification PK-42385-999 (PDF)
Drawing (PDF)	Test Summary 423850000-TS-000 (PDF)
Product Specification PS-5556-002-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification TS-5556-002-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General


Product Family	PCB Receptacles
Series	42385
Application	Board-to-Board, Power
Comments	Solder Type With Pegs
Overview	Mini-Fit Products
Product Name	Mini-Fit BMI
UPC	800753689107

Physical

Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Natural
Durability (mating cycles max)	30
Flammability	94V-2
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Resin	Nylon
Net Weight	2.057/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.20mm
Packaging Type	Tray
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	9.0A
Grounding to PCB	No
Voltage - Maximum	600V AC (RMS)/DC



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[42385](#) Series

Mates With

[42475](#) Panel Mount Plug, [42404](#) Right Angle Header, [42440](#) Vertical Header, [43879](#) Vertical Header, [44068](#) Vertical Header

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	240

Material Info

Engineering Number	42385-10A1
--------------------	------------

Reference - Drawing Numbers

Packaging Specification	PK-42385-999
Product Specification	PS-5556-002-001, TS-5556-002-001
Sales Drawing	SDA-42385-*
Test Summary	423850000-TS-000

This document was generated on 10/17/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION