


002  
PCB TERMINAL  
BLOCKS

# 3.81mm screwless terminal blocks

081  
TERMINAL STRIPS

## Product overview

- Interlocking modules
- Easily breakable to desired number of poles
- Guided pin alignment
- Moulded in green UL94-V0 PA66
- 0.5-2.5mm<sup>2</sup> cable (20-14AWG)
-  approved

095  
WIRE TO BOARD  
CONNECTORS100  
CIRCULAR  
CONNECTORS151  
IP68 CONNECTORS158  
INTERFACE  
MODULES AND  
RELAY BASES


CSTBP381



### SPECIFICATION

Rating	10A/300V
Insulation withstand voltage	AC2000V/1 min
Insulation resistance	500MΩ at DC500V
Operating temperature	-40°C to +115°C
Moulding	UL94-V0 PA66
Pin/contact	Tin plated brass
Recommended PCB hole size	1.2mm

PART NO.	POLES	LENGTH
CSTBP381/2	2	9.2mm
CSTBP381/3	3	13.0mm
CSTBP381/4	4	16.8mm
CSTBP381/5	5	20.7mm
CSTBP381/6	6	24.5mm
CSTBP381/7	7	28.3mm
CSTBP381/8	8	32.1mm
CSTBP381/9	9	35.9mm
CSTBP381/10	10	39.7mm
CSTBP381/11	11	43.5mm
CSTBP381/12	12	47.3mm



## KEY FEATURES

Dual row pins | Screwless actuated cage terminals | Modular design

