

Machine tap extension with internal cooling and h6 shank

For the use of machine taps with internal cooling

ORION[®]

Application:

For extending machine taps in conjunction with deep and difficult to reach threads on CNC and conventional machines, in tapping chucks or quick-change chucks in single part production.



Execution:

- Steel tool holder with collet chuck and clamping nut h6 shank, steel shank of the extension pursuant to DIN for high requirements for process reliability and service life

Advantage:

- Very flexible and fast solution as there is no need to procure special machine taps
- User-friendly handling and short retooling times
- Excellent value for money

Art. no.	13533 524
Brand	ORION
Manufacturer Part Number	13533524
Suitable for DIN 374/376 screw tap	M27
Suitable for screw tap square socket size	16 mm
Size of square	16 mm
Collect depth	52 mm
Collet chuck diameter	20 mm
Collect outer diameter	28 mm
Shank diameter	20 mm
Length	330 mm
Shaft length	100 mm
Gross Weight	1.240 kg
Product Group	1DD

EAN

4053625475711