

Double sided adhesive tape 9088-200

Product Data Sheet

January 2019 Supersedes: May 2017

Product Description

Double sided adhesive tape with polyester carrier and modified acrylic adhesive

Key Features

- High adhesion to nearly every high and low surface energy substrate
- High initial tack
- All purpose tape
- Good UV resistance
- High shear and temperature resistance
- Easy handling and converting due to polyester carrier

Application ideas

- Self- adhesive mounting of furniture trim, sealing profiles and cable ducts
- Bonding and mounting of sales displays and billboards
- Fixing of decorative trims and emblems

Construction

Adhesive Type	Modified Acrylic		
Adhesive side open face 1	0,09 mm		
Adhesive Carrier	Transparent PET 0,012 mm		
Adhesive back side 2	0,09 mm		
Tape Colour	colourless		
Total thickness without liner	0,20 mm		
Release Liner	Glassine paper, white 94 g/m² 0,08 mm		

1 open face side is visible when unwinding the roll. 2 the back side is visible after removing the liner Calipers are average values

Performance Characteristics

Adhesion to Stainless Steel - [N/25 mm]	29
Finat FTM1 - (72h RT, 180° peel angle, 300mm/min, Haul-off speed, 0,05 mm PET)	
Adhesion to Polypropylene - [N/25 mm]	26
Finat FTM1 - (72h RT, 180° peel angle, 300mm/min, Haul-off speed, 0,05 mm PET)	
Adhesion to Polycarbonate - [N/25 mm]	20
Finat FTM1 - (72h RT, 180° peel angle, 300mm/min, Haul-off speed, 0,05 mm PET)	
Adhesion to ABS - [N/25 mm]	24
Finat FTM1 - (72h RT, 180° peel angle, 300mm/min, Haul-off speed, 0,05 mm PET)	
Static Shear Resistance to Stainless Steel - [min]	> 10.000
Finat FTM8 - (RT, 1 kg/1"x1")	
Static shear resistance to stainless steel - [min]	> 10.000
Finat FTM8 - (at 90 °C, 0,5 kg/1"x1".)	
Temperature resistance	Pass
SAFT - (40-180 °C; 2°C/min) 500g /1"x1")	

Solvent Resistance (KBA, Issue March 2014)

Media	Substrate	Immersion time [h]	Immersion temperature [°C]	Visual assessment after 48h reconditioning at RT	
Deionized Water	Glass	1	50 ± 2	no change	
5 % Hydrochloric Acid	Glass	1	20 ± 2	no change	good adhesion
1% Sodium hydroxid	Glass	0,50	20 ± 2	slight delamination of edges	good adhesion
Ethyl Alcohol	Glass	0,25	20 ± 2	sample slightly moved	good adhesion
Premium gasoline, lead - free	Aluminium	0,3	20 ± 2	slight leakage of adhesive adhesive edge swelled (5 %)	good adhesion (95 %)
Diesel	Aluminium	0,5	20 ± 2	slight leakage of adhesive adhesive edge swelled (5 %)	good adhesion (95 %)
Methyl-Ehyl-Ketone	Aluminium	0,5	20 ± 2	slight leakage of adhesive adhesive edge swelled (5 %)	good adhesion (95 %)
Motor oil (HD Oil)	Aluminium	1,00	20 ± 2	no change	good adhesion
5 %Tenside (amphoteric,an-ionic nonionic) in H2O	Glass	0,5	20 ± 2	no change	good adhesion

Temperature resistance	Short term (minutes, max.1 hour): -40 °C – 150 °C Long term (days, weeks): 90 °C				
Storage & Shelf Life	Store at 16 °C – 25 °C and 40-65 % relative humidity in its original box. The product can be stored up to 24 months after production.				
	Note: The shelf life may be shortened if the original packaging is not properly sealed or stored in an environment with high temperatures or humidity				
Precautionary Information	Refer to product label and Material Safety Data Sheet for health ar safety information before using the product. For information please contact your local 3M Office. www.3M.com				
For Additional Information	To request additional product information or to arrange for sales assistance, call Address correspondence to: 3M				
Important Notice	All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the				

questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our

3M United Kingdom PLC

recommendations

2M Centre, Cain Road, Bracknell RG12 8HT United Kingdom

3M Ireland Ltd

The Iveagh Building, 3rd Floor The Park, Carrickmines 18 Ireland

3M Belgium bvba/sprl

Hermeslaan 7 1831 Diegem Belgium

3M Nederland B.V.Molengraaffsingel 29
2629 JD Delft
The Netherlands

3M Svenska AB

Herrjärva torg 4 170 67 Solna Sweden

3M a/s

Hannemanns Allé 53 DK-2300 Copenhagen S. Denmark

3M Norge AS

Tærudgata 16 2004 Lillestrøm Norway

Suomen 3M Oy Keilaranta 6

02150 Espoo Finland

3M Eesti OÜ

product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All

Pärnu mnt. 158 11317 Tallinn Estonia

3M Latvia SIA

K.Ulmaņa gatve 5 Rīga, LV-1004 Latvia

3M Lietuva UAB

A.Goštauto g. 40 Vilnius LT- 03163 Lithuania