

Barracuda

Part No: OMB.915.B05F21

Description:

915MHz 5.9dBi Omni Antenna, with N Type Female Connector

Features:

Suitable to use in Robust Outdoor Environment

Connector: N Type Female

Dimensions: 1094 55mm x Ø26 6mm

Wall and Pole Mount

RoHS and REACH Compliant



1.	Introduction	3
2.	Specifications	4
3.	Antenna Characteristics	5
4.	Radiation Patterns	7
5.	Mechanical Drawing	9
6.	Packaging	10
7.	Antenna Installation Guide	11
	Changelog	12

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.













The Barracuda OMB.915.B05F21 is a fiberglass omnidirectional outdoor antenna, operating in the 915MHz ISM band and is designed to offer long distance coverage. The antenna is designed for applications such as metering, industrial & environmental monitoring, remote asset monitoring and mesh network applications. The 915MHz band is one of the most widely used license free ISM bands. Typical applications are in SigFox, Helium, LoRa and LPWA networks.

With a 5.9dBi peak gain, the OMB.915.B05F21omnidirectional antenna radiates uniformly in the azimuth. This collinear design characteristic provides the best performance, giving optimized coverage and therefore longer range in the horizontal plane over 360 degrees, thus minimizing the amount of nodes needed for a mesh network. The UV resistant fiberglass housing enables the OMB antenna to be utilized in all kinds of harsh environments making it more robust and safer than traditional whip antennas. It can be connected directly to the access point or telemetry unit or can be mounted on wall or device surface via the N-type connector and a pole-mount and wall-mount bracket is included. This antenna is an ideal product for developing your own Helium Network on the 915MHz spectrum.

Custom antenna modifications are subject to possible NRE and minimum order quantity. For further information please contact your regional Taoglas customer support team.




2. Specifications

Electrical											
Frequency (MHz)	Band	Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	Impedance	Polarization	Radiation Pattern	Max Input Power			
915MHz	902-928	75.7	-1.21	5.9	50Ω	Linear	Omni	30W			
Mechanical											
I	Length			1094±30mm							
Bracke	Bracket Dimension			70*54mm							
Radon	Radome Diameter			24mm							
Anter	Antenna Weight			500g							
Mounting Accessories			70g								
Application			Indoor/Outdoor								
Radome Material			White Fiberglass								
Base Material			Aluminium								
Mo	Mount Style			Pole Mount/Wall Mount							
Mounting			Stainless Steel								
Wind	Wind Resistance			>150mph (>241km/h)							
Wa	Waterproof			IP65							
Environmental											
Storage	Storage Temperature			-20°C to +80°C							
Operating Temperature			-20°C to +60°C								
Operating Humidity			10%~80% Non-condensing								
Storag	Storage Humidity			5%~80% Non-condensing							




3. Antenna Characteristics

3.1 Return Loss




3.2 Efficiency






3.3 Average Gain




3.4 Peak Gain





4. Radiation Patterns

4.1 Test Setup





Free space



8


4.2 915MHz_2D & 3D Radiation Patterns







5. Mechanical Drawing (Units: mm)







10

6. Packaging

1pcs OMB.915.B05F21 per Tube Dimensions – Ø80*1150



10pcs OMB.915.805F21 per carton Dimensions - 1170*410*180mm





Antenna Installation Guide 7.

Installation Instructions **Barracuda OMB Series** Omni-directional Outdoor Antenna




) Introduction

The Barracuda OMB Antenna is an omnidirectional, fibreglass, outdoor antenna. The UV resistant fibreglass housing enables the OMB antenna to be utilized in all kinds of harsh environments, making it more robust and safer than traditional whip antennas. The omnidirectional antenna's collinear dipole design allows it to radiates uniformly in the azimuth with a high gain, providing coverage over long distances, thus minimizing the number of cells or nodes needed in a network. The antenna has an integrated aluminium bracket to be directly installed on a pole, designed to offer a secure, high wind resistant mount.



) Mounting & Location

To ensure prime performance, the Barracuda OMB series should be mounted in a clean location that is clear from all obstruction so that there is no impact on radiation performance. Also, before installing there must be at least 15mm clearance of all metallic objects around the location. When mounting the bracket on the pole, make sure to keep the bracket level with the top of the pole. The bracket should be mounted on the pole using the following list that are all supplied by Taoglas.



2 M6 U-Bolt

4 Washers

4 M6 Nuts

1 Barracuda Antenna

) Mount Alignment

When mounting the antenna it is important that the top of the aluminium bracket is aligned with the top of the pole. The top of the pole should not exceed the top of the mounting bracket as it will interfere with the with the antennas performance.

See image for reference of correct mount alignment.



D) Installation of the Antenna

Put the two U-Bolts around the pole and through the holes in the aluminium bracket. Making sure that the bracket is correctly positioned level to the top of the pole, place one of the four washers provided, over each of the threaded ends of the U-bolts. Then screw on of the four M6s nuts provide on to each threaded end of the U-bolts and tighten in place.



Barracuda/IG-22-8-002 www.taoglas.com

www.taoglas.com SPF-22-8-119-A

11



12

E) Securing the Mount

In order to make sure that the antenna is firmly secured in place on the top of the pole, ensure that the four M6 nuts have been fully tightened. The bracket should not move or shake at all once properly installed.



G) Notices



Caution

To comply with FCC RF Exposure requirements in section 1.1310 of the FCC Rules, antennas used with this device must be installed to provide a separation distance of at least 20 cm from all persons to satisfy RF exposure compliance.



Warning

Do not Operate the transmitter when someone is within 20 cm of the antenna. **Do not** operate the equipment in an explosive atmosphere.



European Waste Electronic Equipment Directive 2002/96/EC

Please ensure that your old Waste Electricals and Electronics are recycled do not throw them away into standard waste.



Directive 2014/53/EU Radio Equipment Directive (RED)

Harmonised Standards and References:

EN 301 489-1 (V2.2.1): ElectroMagnetic Compatibility (EMC) standard for radio equipment and services; Part 1: Common technical requirements. Referencing CENELEC EN 55032 Class B.

Waiver: This document represents information compiled by Taoglas to the best of our current knowledge. This is not intended to be used as a representation or warranty of fitness of the products described for any particular purpose. This document details guidelines for general information purposes only. When planning installations, always seek specialist advice and ensure that the products are always installed by a properly qualified installer in accordance with applicable regional laws and regulations.

All copyrights, trademarks and any other intellectual property rights related are owned by Taoglas Group Holdings Limited.

Barracuda/ IG-22-8-002 www.taoglas.com



Changelog for the datasheet

SPE-22-8-119 – OMB.915.B05F21 Revision: A (Initial Release) Date: 2022-08-02 Changes: Initial Release Changes Made by: Gary West

Previous Revisions					



www.taoglas.com

