

SVJC clamp holder positive, left-hand

For copying, longitudinal and face turning with VC indexable insert

ATORN[®]

Application


For copying, longitudinal and face turning with VC indexable insert 35°

Version

- Precision-manufactured steel support, burnished, hardened, type V, working angle 93°, tip angle 35°, clearance angle 7°

Advantage

- Very slim geometry, optimised for contour turning work
- Positive body geometry ensures low cutting forces
- Very good surfaces, for medium and finishing infeed



Art. no.	17833 037
ISO name	SVJC R/L2020 K11
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	23 mm
Programming size	25 mm
Suitable for indexable inserts	VC.. 1103..
Tool design	Left
DIN	4983

EAN-Code

4050293346664