

## Pneumatic-hydraulic blind rivet nut placement tool

Taurus 3 model



### Application:

For rapid placement of blind rivets made of all materials up to 6.4 mm in diameter.

### Execution:

- Powerful, patented gripping mechanism and chuck jaw system
- The complete device stroke is used to place the rivet
- Compressed air-saving technology; air required to place the rivet is also used to eject the riveting mandrel
- Extremely low noise emissions.
- High placement forces with lightweight device



<b>Art. no.</b>	<b>53195 057</b>
<b>Brand</b>	GESIPA
<b>Manufacturer Part Number</b>	1457871
<b>Model</b>	Taurus 3
<b>Suitable for min./max. rivet diameter</b>	4.8-6.4 mm
<b>Rivet setting force</b>	18000 N
<b>Max. working stroke</b>	25 mm
<b>Min./max. operating pressure</b>	5-7 bar
<b>Weight</b>	1.9 kg
<b>Gross Weight</b>	3.340 kg
<b>Product Group</b>	561

### EAN

4007081580007

