

Test pumps HP 500, 0 to 200 bar

With 30-L oval container or 60-L rectangular container



Application:

For hydrostatic testing of parts such as fittings, pipes, pipelines, tanks, gas bottles, test stands and many other high-pressure components.

Execution:

- Test media: clear water, water/oil emulsion, hydraulic oil or low viscosity oil
- With drain valve, pressure gauge and hot-dip galvanised container

Advantage:

- 2-stage pumps with large piston for rapid filling of the system being tested and small piston for building the test pressure



Art. no.	56377 110
Brand	URACA
Manufacturer Part Number	W2853-K1 +ZUBEHÖR
Model	HP 500
Bin capacity	60 l
Min./max. pressure	2-200 bar
Design	Mobile
Connection thread	G 3/8 inch
Form	Rectangular
Feed volume per stroke	79 cm ³
Length x width x height	480 x 330 x 490 mm
Material	Sheet steel
Weight	31 kg
Gross Weight	18.000 kg
Product Group	575