

Ultra-grip sets of ratchet fork box wrenches, 10 and 12 pcs

With two-sided clamping function



Version:

- Non-slip fork. Does not slip over the nuts, provides optimum safety.
- Ring end with spring clamping ring – the nut is securely held in the ring
- Ring head with reversible ratchet mechanism, finely serrated (72 teeth) and return angle 5° (7.5° for 6 mm, 6° for 7, 8 and 9 mm).
- Inclination of ring and fork: 15°.

Delivery:

In a functional folding holder (pocket case)



Art. no.	52050 212
Width across flats	7 mm, 8 mm, 10 mm, 11 mm, 12 mm, 13 mm, 14 mm, 15 mm, 16 mm, 17 mm, 18 mm, 19 mm
Number of pieces in assortment/set	12 PCS
Surface	Chrome plated
Material	Chrome-vanadium steel

EAN-Code

3662424068393