

5VK7 ✓ ACTIVE

[Corcom](#) | [Corcom K](#)

TE Internal #: 1-6609028-1

Corcom K, Single Phase Filters, 5A Filter Current Rating, Bulkhead, IEC Input, .250" FASTON Output, Leakage Current (Max) (120VAC, 60Hz) .4 mA

[View on TE.com >](#)



[EMI Filters](#) > [Power Line Filters](#) > [Single Phase Filters](#) > [CORCOM K SERIES SINGLE PHASE FILTERS](#)



Filter Current Rating: 5 A

Filter Mount Style: **Bulkhead**

Filter Input Termination Type: IEC

Filter Output Termination Type: .250" FASTON

Leakage Current (Max) (120VAC, 60Hz): .4 mA

[All CORCOM K SERIES SINGLE PHASE FILTERS \(42\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Filtering Requirements	Filtered
Filter Input Termination Type	IEC
Filter Output Termination Type	.250" FASTON

Electrical Characteristics

Voltage (Max)	250 VAC
Filter Current Rating	5 A
Leakage Current (Max) (120VAC, 60Hz)	.4 mA
Leakage Current (Max) (250VAC, 50Hz)	.7 mA

Mechanical Attachment

Filter Mount Style	Bulkhead
--------------------	----------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Corcom K



Single Phase Filters(42)


Customers Also Bought



TE Part #1-5747150-3
D-Sub Receptacle Assembly: Vertical,
Shell Size 1, 2.74mm



TE Part #1-6609028-2
CORCOM K SERIES SINGLE PHASE
FILTERS



TE Part #1-583717-3
TW LEAF CRP HSG. 30-POS.



TE Part #1-5745967-4
D-Sub Receptacle Assembly: Vertical,
Shell Size 3, 2.77mm



TE Part #1-1419108-7
RT424024F



TE Part #104257-2
03 MTE RCPT HSG SR LATCH .100



TE Part #1-87499-1
06 MODIV HSG SR MRKD .100CL



TE Part #1-2364570-5
AVH19 FLT SS MT RNG GRN 24V16A



TE Part #1-2364570-9
AVH19 FLT SS MT RNG BLU 24V16A



TE Part #BGC880N0000052A000
917 RECEPTACLE, ANGLED,
ROTATABLE

Documents

Product Drawings

5VK7=F7141 S0

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-6609028-1_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-6609028-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-6609028-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE](#)

English

[1654001_CORCOM_PRODUCT_GUIDE_K_SERIES](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English

[Corcom Combined Selector Charts](#)

English