PRODUCT CA17722_EMERALD-ER2-PC

EMERALD-ER2-PC

Rectangular beam for escape routes with greater than 5 m mounting height. Assembly with installation tape.

SPECIFICATION:

Dimensions Ø 21.6 mm 9.3 mm Height Fastening glue, pin yes 🕕 **ROHS** compliant



MATERIALS:


Material Colour **Finish** Component **Type EMERALD-ER2-PC** Single lens PC clear **HEIDI-TAPE** Tape Acrylic foam black

ORDERING INFORMATION:

Component Qty in box MOQ MPQ Box weight (kg) 3456 288 144 8.8 CA17722_EMERALD-ER2-PC Single lens » Box size: 480 x 280 x 300 mm



PRODUCT CA17722_EMERALD-ER2-PC



See also our general installation guide: www.ledil.com/installation_guide


2/5

OPTICAL RESULTS (SIMULATED):



LED XHP35 HD
FWHM / FWTM Asymmetric
Efficiency 85 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour White


Required components:



CREE + LED

LED XHP35 HI
FWHM / FWTM Asymmetric
Efficiency 86 %
Peak intensity 1.8 cd/lm
LEDs/each optic 1
Light colour White


Required components:



CREE + LED

LED XP-G3
FWHM / FWTM Asymmetric
Efficiency 86 %
Peak intensity 1.7 cd/lm
LEDs/each optic 1
Light colour White

Required components:




CREE - LED

.ED XT-E

FWHM / FWTM 125.0 + 16.0° / 139.0 + 23.0°

Efficiency 86 %
Peak intensity 1.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:



Published: 18/01/2021




OPTICAL RESULTS (SIMULATED):

OSRAM Opto Semiconductors

LED OSLON Square CSSRM2/CSSRM3


 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ Asymmetric Efficiency 86 % 2.1 cd/lm Peak intensity LEDs/each optic Light colour White

Required components:



SAMSUNG

LED LH351B FWHM / FWTM Asymmetric Efficiency 84 % 1.6 cd/lm Peak intensity LEDs/each optic 1 Light colour White Required components:



Published: 18/01/2021



PRODUCT DATASHEET CA17722 EMERALD-ER2-PC

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405, Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy