


Model Number

CBN15-30GK60-E0

Features

- 15 mm not embeddable
- Operating distance adjustable via potentiometer
- High EMC resistance

Connection




Accessories

BF 30

Mounting flange, 30 mm

Dimensions



Technical Data

General specifications

Switching element function		NPN	NO
Rated operating distance	s_n	15 mm	
Installation		not embeddable	
Output polarity		DC	
Assured operating distance	s_a	0 ... 12.1 mm	

Nominal ratings

Installation conditions			
A		18 mm	
B		10 mm	
C		30 mm	
F		60 mm	
Operating voltage	U_B	10 ... 30 V DC	
Switching frequency	f	0 ... 10 Hz	
Reverse polarity protected		reverse polarity protected	
Short-circuit protection		pulsing	
Voltage drop	U_d	≤ 2.8 V	
Operating current	I_L	0 ... 200 mA	
Off-state current	I_r	0 ... 0.5 mA typ. 0.1 μ A at 25 °C	
No-load supply current	I_0	≤ 20 mA	
Indication of the switching state		LED, yellow	

Indicators/operating means

Potentiometer	sensitivity adjustment
---------------	------------------------

Ambient conditions

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
Storage temperature	-40 ... 85 °C (-40 ... 185 °F)

Mechanical specifications

Connection type	cable PVC , 2 m
Core cross-section	0.75 mm ²
Housing material	PBT
Sensing face	PBT
Protection degree	IP67

Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007

Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	Products with a maximum operating voltage of ≤ 36 V do not bear a CCC marking because they do not require approval.

Installation conditions

