



## Section 1. Product and Company Identification.

**1.1 Model Number;** SSW80 v1  
**1.2 Description;** Hand Wipes Heavy-Duty Pack of 80

### 1.3 Manufacturer;

Sealey Group.  
Kempson Way,  
Bury St. Edmunds,  
Suffolk.  
IP32 7AR

**1.4 Emergency telephone number;** 44 (0) 1284 757 500 (Office Hours)

**Date of source compilation;** 15/05/2017

## Section 2. Hazards Identification.

### 2.1 Classification of the substance or mixture.

Eye Irrit. 2: H319  
Causes serious eye irritation.

### 2.2 Label elements.

#### Hazard pictogram(s)



**Signal Word.** Warning

#### Hazard statements;

H319 Causes serious eye irritation.

#### Precautionary statements;

P264: Wash hands thoroughly after handling.  
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes.  
Remove contact lenses, if present and easy to do. Continue rinsing.  
P337+313: If eye irritation persists: Get medical advice.

### 2.3 Other hazards.

This product is not identified as a PBT/vPvB substance.



### Section 3. Substances.

3.1 Chemical Name (substance)	3.1 CAS No.	3.2 Concentration Weight	Classification	
			Hazard Class & Category Code	Hazard Statements <sup>1</sup>
propan-2-ol; isopropyl alcohol; isopropanol	67-63-0	1 – 10 %	Flam. Liq. 2 STOT SE 3 Eye Irrit. 2	H225 H336 H319
Benzalkonium Chloride	68424-85-1	< 1 %	Acute Tox. 4 Skin Corr. 1B Acute Tox. 4	H302 H314 H312

<sup>1</sup>For full text of Phrases and Statements, see Section 16.

### Section 4. First Aid Measures.

#### 4.1 Description of first aid measures

##### Inhalation

Move to fresh air in case of accidental inhalation of vapours.

##### Skin Contact

In case of allergy, drench the affected skin with water

##### Eye Contact

Bathe the eye with running water for 15 minutes.

##### Ingestion

As the substrate is a wipe material, ingestion is highly unlikely

Do not induce vomiting.

Wash mouth out with water.

Seek medical advice.

#### 4.2. Most important symptoms and effects, both acute and delayed

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest.

**Eye contact:** There may be irritation and redness.

**Skin contact:** There may be mild irritation at the site of contact.

**Ingestion:** There may be irritation of the throat.

#### 4.3. Indication of any immediate medical attention and special treatment needed

Not applicable.



## Section 5. Fire Fighting Measures.

### 5.1. Extinguishing media

Use suitable fire extinguisher for the surrounding fire.

### 5.2. Special hazards arising from the substance or mixture

Emits toxic fumes during combustion.

### 5.3. Advice for fire-fighters

Wear self-contained breathing apparatus.

Wear protective clothing to prevent contact with skin and eyes.

## Section 6. Accidental Release Measures.

### 6.1. Personal precautions, protective equipment and emergency procedures

No data available.

### 6.2. Environmental precautions

Do not discharge into drains or water courses.

### 6.3. Methods and material for containment and cleaning up

Transfer to a closable, labelled container for disposal.

### 6.4. Reference to other sections

See Section 7 for information on Safe Handling

See Section 8 for information of Personal Protective Equipment.

See Section 13 for information on disposal.

## Section 7. Handling and Storage.

### 7.1. Precautions for safe handling

Avoid formation or spread of dust in the air.

### 7.2. Conditions for safe storage, including any incompatibilities

Store in a cool. Well ventilated area.

### 7.3. Specific end use(s)

Intended for use as Hand Wipes, Model Number identified in 1.1 with Description stated in 1.2.



## Section 8. Exposure Controls/Personal Protection.

### 8.1. Control parameters

Workplace exposure limits:

8 hour TWA: 999 mg/m<sup>3</sup>

15 min. STEL: 1250 mg/m<sup>3</sup>

### 8.2. Exposure controls

#### Appropriate Engineering Controls

Ensure adequate ventilation.

#### Eye/Face Protection

Not required under normal use.

#### Skin Protection

Not required under normal use.

#### Respiratory Protection

Not required under normal use.

## Section 9. Physical and Chemical Properties.

### 9.1. Information on basic physical and chemical properties

**The following information is not a technical specification or sales specification.**

(a) Appearance:	Wet, non-woven wipes.
(b) Odour:	Sweet smelling.
(c) Odour threshold;	No data available.
(d) pH:	No data available.
(e) Melting point/freezing point;	No data available.
(f) Initial boiling point and boiling range;	No data available.
(g) Flash point;	41°C
(h) Evaporation rate;	No data available.
(i) Flammability (solid, gas);	No data available.
(j) Upper/lower flammability or explosive limits;	No data available.
(k) Vapour pressure;	No data available.
(l) Vapour density;	No data available.
(m) Relative density;	No data available.
(n) Solubility in water;	Solution used to impregnate wipes is miscible.
(o) Partition coefficient: n-octanol/water;	No data available.
(p) Auto-ignition temperature;	No data available.
(q) Decomposition temperature;	No data available.
(r) Viscosity;	No data available.
(s) Explosive properties;	No data available.
(t) Oxidising properties.	Non-Oxidising.

### 9.2 Other information

No data available.



## Section 10. Stability and Reactivity.

10.1. Reactivity	No data available.
10.2. Chemical stability	Stable under recommended transport and storage conditions.
10.3. Possibility of hazardous reactions	Hazardous reactions will not occur under recommended transport and storage conditions
10.4. Conditions to avoid	Heat.
10.5. Incompatible materials	Strong oxidising agents. Strong acids.
10.6. Hazardous decomposition products	Emits toxic fumes during combustion.

## Section 11. Toxicological Information.

### 11.1. Information on toxicological effects

Propan-2-ol

Oral Mus LD50 3600 mg/kg

Oral Rat LD50 5045 mg/kg

Symptoms / routes of exposure.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest.

**Eye contact:** There may be irritation and redness.

**Skin contact:** There may be mild irritation at the site of contact

**Ingestion:** There may be irritation of the throat.

## Section 12. Ecological Information.

12.1. Toxicity	No data available.
12.2. Persistence and degradability	No data available.
12.3. Bioaccumulative potential	No data available.
12.4. Mobility in soil	No data available.
12.5. Results of PBT and vPvB assessment	Not identified as PBT / vPvB substance.
12.6. Other adverse effects	No data available.

## Section 13. Disposal Considerations.

### 13.1. Waste treatment methods

Dispose in accordance with local authority regulations.



**Section 14. Transport Information.**

Product does not require transport classification.

**Section 15. Regulatory Information.**

**15.1.** Safety, health and environmental regulations/legislation specific for the substance or mixture  
No data available.

**15.2.** Chemical safety assessment  
No data available.

**Section 16. Additional Information.**

Full text of Phrases and Statements used in Section 3;

- H225 Highly flammable liquid and vapour.
- H302 Harmful if swallowed.
- H314 Causes severe skin burns and eye damage.
- H312 Harmful in contact with skin.
- H319 Causes serious eye irritation.
- H336 May cause drowsiness or dizziness.

The above information is believed to be accurate and represents the best information currently available.  
No warranty is expressed or implied by the above information.  
We assume no liability resulting from use of the above information.  
The end user should conduct their own investigations to determine the suitability of the above information for their particular purpose.

Issue level	Date	Revisions
1	14/09/18	First issue.

End of Safety Data Sheet.