




Fibre optic through beam sensor

FE-11-EPA-M6/F1x1/2M



1 glass lens

Application

Function principle Through-beam sensor

Detection zone

Range with fibre optic amplifier type OB50; OBF; OO50

OB50

Range of fibre optics [mm] 1200

OBF

Range of fibre optics [mm] 2000

OO50

Range of fibre optics [mm] 3800

Operating conditions

Ambient temperature [°C] -40...70

E20752



Fibre optic through beam sensor

FE-11-EPA-M6/F1x1/2M

Mechanical data	
Weight [g]	54.5
Version of sensing head	straight
Sensing head thread	M6
Total length [mm]	2000
Min. bending radius [mm]	30
Fibre arrangement	●
Core diameter [mm]	1
Fibre material	PMMA
Fibre head material	aluminium
Fibre sheath material	PE
Accessories	
Accessories (supplied)	hexagon nuts: 2 x M6, stainless steel tooth lock washers: 2
Accessories (optional)	Cutter for fibre optics, E20600
Remarks	
Pack quantity	1 pcs.