

Flexible extractor arm

With fan, 750 W



Application:

For selective capturing and extraction of smoke, dust, gases, vapours and welding fumes. Polluted air is captured at the point of origin and blown into the open air.

Version:

- Three-phase AC motor
- Voltage 230 V, frequency 50 Hz
- Extractor arm consists of 3 joints
- Internal support linkage made from aluminium
- A fibreglass cloth hose is slipped over the linkage
- The extractor hood with integrated throttle flap can be swivelled in any direction on a self-supporting basis
- For wall mounting

Advantage:

- The extractor arm can easily be adjusted to any position thanks to the favourable arrangement of springs

Delivery:

1 low-wear, self-lubricating rotary flange



Art. no.	75741 010
Air supply quantity	2000 m ³ /h
Height	2925 mm
Extraction arm length	2 m
Ventilator weight	28 kg
Extraction arm weight	20 kg