

PC824/PC844

AC Input Photocoupler

* Lead forming type (I type) and taping reel type (P type) are also available.

■ Features

1. AC input
2. High isolation voltage between input and output (V_{iso} (rms): 5kV)
3. Compact dual-in-line package
PC824 (2-channel type)
PC844 (4-channel type)
4. Current transfer ratio
 CTR: MIN. 20% at $I_F = \pm 1\text{mA}$, $V_{CE} = 5\text{V}$
5. Recognized by UL, file No. E64380

■ Applications

1. Programmable controllers
2. Telephones
3. Facsimiles

■ Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)


Parameter	Symbol	Rating	Unit
Forward current	I_F	± 50	mA
*1 Peak forward current	I_{FM}	± 1	A
Power dissipation	P	70	mW
Collector-emitter voltage	V_{CEO}	35	V
Emitter-collector voltage	V_{ECO}	6	V
Collector current	I_C	50	mA
Collector power dissipation	P_C	150	mW
Total power dissipation	P_{tot}	200	mW
*2 Isolation voltage	V_{iso} (rms)	5	kV
Operating temperature	T_{opr}	-30 to +100	°C
Storage temperature	T_{stg}	-55 to +125	°C
*3 Soldering temperature	T_{sol}	260	°C

*1 Pulse width $\leq 100\mu\text{s}$, Duty ratio: 0.001

*2 40 to 60%RH, AC for 1 minute

*3 For 10s

■ Outline Dimensions (Unit : mm)





Notice In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc. Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.
 Internet address for Electronic Components Group <http://sharp-world.com/ecg/>







SHARP**PC824/PC844****■ Electro-optical Characteristics**






(T _a =25°C)							
	Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Input	Forward voltage	V _F	I _F =±20mA	—	1.2	1.4	V
	Peak forward voltage	V _{FM}	I _{FM} =±0.5V	—	—	3.0	V
	Terminal capacitance	C _t	V=0, f=1kHz	—	50	250	pF
Output	Collector dark current	I _{CEO}	V _{CE} =20V, I _F =0	—	—	100	nA
	Collector current	I _C	I _F =±1mA, V _{CE} =5V	0.2	—	3.0	mA
Transfer characteristics	Collector-emitter saturation voltage	V _{CE(sat)}	I _F =±20mA, I _C =1mA	—	0.1	0.2	V
	Isolation resistance	R _{ISO}	DC500V, 40 to 60%RH	5×10 ¹⁰	10 ¹¹	—	Ω
	Floating capacitance	C _f	V=0, f=1MHz	—	0.6	1.0	pF
	Cut-off frequency	f _c	V _{CE} =5V, I _C =2mA, R _L =100Ω, -3dB	15	80	—	kHz
	Response time	Rise time Fall time	V _{CE} =2V, I _C =2mA, R _L =100Ω	—	4	18	μs
				—	3	18	μs

■ Rank Table(I_F=±1mA, V_{CE}=5V, T_a=25°C)

Model No.	Rank mark	I _C (mA)
PC824A	A	0.5 to 1.5
PC844A		
PC824	A or no mark	0.2 to 3.0
PC844		

Fig.1 Forward Current vs. Ambient Temperature**Fig.2 Collector Power Dissipation vs. Ambient Temperature**

SHARP**PC824/PC844****Fig.3 Peak Forward Current vs. Duty Ratio****Fig.4 Forward Current vs. Forward Voltage****Fig.5 Current Transfer Ratio vs. Forward Current****Fig.6 Collector Current vs. Collector-emitter Voltage****Fig.7 Relative Current Transfer Ratio vs. Ambient Temperature****Fig.8 Collector-emitter Saturation Voltage vs. Ambient Temperature**

SHARP**PC824/PC844****Fig.9 Collector Dark Current vs. Ambient Temperature****Fig.10 Collector-emitter Saturation Voltage vs. Forward Current****Fig.11 Response Time vs. Load Resistance****Test Circuit for Response Time****Fig.12 Frequency Response****Test Circuit for Frequency Response**