

EAN CODE : 3760244880406 (DR04)



ACCURACY 1% DR 04/05/06/07/08

EAN CODES : 3760244880413 (DR05)  
 3760244880420 (DR06)  
 3760244880437 (DR07)  
 3760244880444 (DR08)



- ROBUST** : Metal case, epoxy finish.
- PRECISE** : Good long-term stability.
  - 1% resistors.
- EASY** : front panel.
  - Intermediate tap at each decade.

**ROBUSTS**  
**RESISTANCE** from  
 0,1 Ohm to  
 11,111 111 MOhms



## Specifications

- The DR04-07 boxes use metal film resistors offering 0.5% accuracy and a temperature coefficient of 50 ppm/°C.
- The DR08 box use thick film resistors offering 1% accuracy and a temperature coefficient of 100 ppm/°C
- Output of each decade on 4 mm safety socket.
- Screen outputs (front panel and case) on safety earth socket.
- Professional quality switches with gilt contacts. (R < 9 mΩ).
- Max power rating : 0.5 W.

## Other specifications

- Safety : Complies with EN 61010-1, Overvoltage category III, pollution degree 2.
- Max voltage : DR04-07, 150 V AC/DC (reinforced insulation). 250 V AC/DC with earth connected to safety earth socket (single insulation). DR08, 300 V AC/DC (reinforced insulation)
- Presentation : aluminium mounting plate, screen-printed satin epoxy finish, metal case, epoxy finish.

Type	Weight Kg	Decades	Multiplier in OHMS								Totale Resistance
			0.1	1	10	100	1 K	10 K	100 K	1M	
DR 04	1	4		•	•	•	•				11,110 KΩ
DR 05	1,4	5		•	•	•	•	•			111,110 KΩ
DR 06	1,44	6		•	•	•	•	•	•		1 111,110 KΩ
DR 07	1,52	7		•	•	•	•	•	•	•	11,111 110 MΩ
DR 08	1,4	8	•	•	•	•	•	•	•	•	11,111 111 MΩ
Accuracy %			3	1	1	1	1	1	1	1	
Max current			2.3 A	700 mA	200 mA	70 mA	20 mA	7 mA	2 mA	0,7 mA	

- The assembly is mounted on the front panel which fits into a 19" standard subrack.
- Mounting plate dimensions :

DR04 : H = 2U (U = 44.45 mm) - L = 84F (F = 5.08 mm)  
 DR 05, 06, 07, 08 : H = 2U (U = 44.5 mm) - L = 84F (F = 5.08 mm)

