

SSM1A312BDR

Solid state modular relay, 12 A, random switching, input 4...32 V DC, output 48...600 V AC



Main

Range of product	Harmony Relay
Product or component type	Solid state relay
Device short name	SSM
Number of channels	1
Number of phases	1 phase

Complementary

Mounting support	Symmetrical DIN rail
Line Rated Current	12 A
Output voltage	48...600 V AC
[Uc] control circuit voltage	4...32 V DC
Contacts type and configuration	1 NO
Tightening torque	0.5...0.8 N.m input 0.5...0.8 N.m output
Connections - terminals	Screw terminals 1 x 0.3...1 x 1.5 mm ² , AWG 22...AWG 16) input Screw terminals 1 x 0.3...1 x 2.5 mm ² , AWG 22...AWG 14) output
Maximum capacitance	10 pF input/output
Insulation resistance	1000 MOhm 500 V DC
Local signalling	Input status LED green)
Minimum switching voltage	4 V DC turn-on
Maximum switching voltage	1 V DC turn-off
Input current	9...11 mA
Solid state output type	SCR output Random voltage switching
Load current	0.15...12 A
Transient overvoltage	1200 V
Surge current	715 A 16.6 ms 750 A 20 ms
Maximum voltage drop	<1.3 V on-state
Maximum Horse Power Rating	0.33 hp 104 °F (40 °C) 240 V AC
Maximum I ² t for fusing	2560 A ² .S 10 ms 50 Hz 2330 A ² .s 8.33 ms 60 Hz
Maximum leakage current	0.2 mA off-state
DV/dt	500 V/μs off-state at maximum voltage
Response time	0.5 cycle turn-off) 0.1 ms turn-on)
Power factor	0.5 with maximum load)
Overvoltage category	III
Maximum Width	0.71 in (18 mm)
Height	3.56 in (90.3 mm)
Depth	3.30 in (83.7 mm)
Net Weight	0.20 lb(US) (0.09 kg)

Environment

Flame retardance	V0 UL 94
Dielectric strength	4 KV AC input/output 4 kV AC input or output to case
Pollution degree	2
Standards	IEC 62314 IEC 60950-1 IEC 61000
Product certifications	UL CSA
Marking	CE
IP degree of protection	IP20
Ambient air temperature for operation	-22...176 °F (-30...80 °C)
Ambient air temperature for storage	-22...212 °F (-30...100 °C)

Ordering and shipping details

Category	22375 - INTERFACE MODULE(ABA,R,S)
Discount Schedule	CP2
GTIN	00785901952442
Nbr. of units in pkg.	1
Package weight(Lbs)	0.2 lb(US) (0.09 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	0.200 dm
Package 1 width	0.900 dm
Package 1 Length	0.900 dm


Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Dimensions



Derating Curves



A : Load Current (Amperes)

B : Ambient Temperature (°C)

1 : Multiple units, no minimum spacing between components

2 : Installed single unit, distance to adjacent components more than 18 mm