

Beacon LED XL

BEACON XL 93CRI 3K MEDIUM BEAM L3+DALI BLACK
2059686



Product features

- Integrated LED spotlight, black RAL 9005, compact and minimalist design, ideal for retail, display, museum and gallery applications, die-cast aluminium body, passive cooling heatsink, beam angle: 34° medium beam, optics: Polycarbonate lens, colour temperature: 3000K warm white, total system power: 33W, total fixture output: 3060lm, luminaire efficacy: 93lm/W, LOR: 100%, colour rendering: Ra 93 typical, LED Chromacity: 3 step MacAdam ellipse, IR/UV free light source without heat radiation, operating voltage: 220-240V / 50-60Hz, drive current: 800mA, electronic driver, DALI dimmable, power factor: 0.9 electrical protection: CLASS II, 3-circuit DALI track adaptor, suitable for Concord Lytespan 3+DALI track, ingress protection rating: IP20. **IMPORTANT NOTE:** This fixture can only be used on the Lytespan DALI or Lytebeam DALI tracks !



PRODUCT OVERVIEW

Product name	BEACON XL 93CRI 3K MEDIUM BEAM L3+DALI BLACK
Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Museums & Galleries, Retail
ETIM Class	EC001744
E-number FI	4280846
Warranty	5 years
Fixture luminous flux (lm)	3060
Luminaire efficacy (lm/W)	93
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	93
Colour Consistency (SDCM)	3
Beam Angle (°)	34
Photobiological Risk Group	RG1
Total power consumption (W)	33
Product Voltage (V)	240
Electrical protection	Class II
Control gear type	Electronic ballast
Dimmable	Yes
Dimming method	DALI
Minimum dimming level (%)	1
Housing colour	Black
IP rating	IP20
IK rating	IK02
Product EAN number	5025768596867

Beacon LED XL

BEACON XL 93CRI 3K MEDIUM BEAM L3+DALI BLACK

2059686

DATA TABLE

General data

Product name	BEACON XL 93CRI 3K MEDIUM BEAM L3+DALI BLACK
Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Museums & Galleries, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
E-number FI	4280846
Warranty	5 years

Optical data

Fixture luminous flux (lm)	3060
Luminaire efficacy (lm/W)	93
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	93
Colour Consistency (SDCM)	3
Adjustable chromaticity	N
Beam Angle (°)	34
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	33
Mains voltage (V)	220-240V
Product Voltage (V)	240
Lamp power factor	0.9
Electrical protection	Class II
Control gear type	Electronic ballast
Transformer required	Yes
Dimmable	Yes
Dimming method	DALI
Minimum dimming level (%)	1
Drive current (mA)	800
Inrush Current (A)	20
Inrush Duration (µs)	50
Glow Wire Test (°C)	650
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	33
Max. Luminaires per 16A C Breaker	55
Max. Luminaires per 10A B Breaker	33
Max. Luminaires per 16A B Breaker	55

Beacon LED XL

BEACON XL 93CRI 3K MEDIUM BEAM L3+DALI BLACK

2059686

Lifetime data

Lifespan L70 B50	72000
Lifespan L80 B20	72000
Lifespan L90 B10	33000


Physical data

Housing colour	Black
IP rating	IP20
IK rating	IK02
Nominal Product Length (mm)	85
Nominal Product Width (mm)	165
Nominal Product Height (mm)	205
Nominal Product Diameter (mm)	113
Weight (kg)	1.365

Packaging

Single packaging type	Carton
Product EAN number	5025768596867
Packaging single length / height (cm)	25.0
Packaging single width (cm)	19.5
Packaging single depth (cm)	20.0
DUN14 (outer)	05025768596867
Units per outer package	1
Packaging outer length / height (cm)	25.0
Packaging outer width (cm)	19.5
Packaging outer depth (cm)	20.0

PHOTOMETRY



Distance [m]	Cone diameter [m]	E ₀ [lx]	E _{10°} [lx]	E _{30°} [lx]
0.5	0.31	2693	17.2°	10842
1.0	0.61	6188	17.2°	2710
1.5	0.92	2740	17.2°	1204
2.0	1.22	1541	17.2°	678
2.5	1.53	967	17.2°	434
3.0	1.83	635	17.2°	301

Distance [m] Cone diameter [m] Illuminance [lx]
C0 - C180 (Half beam angle: 34.0°)

TECHNICAL DRAWINGS

Beacon LED XL

BEACON XL 93CRI 3K MEDIUM BEAM L3+DALI BLACK
2059686

