

Tap wrench Basic Steel

For holding square-head screw taps and reamers in accordance with DIN 10

ORION[®]

Application:

For holding square-head screw taps in accordance with DIN 10, reamers, screw extractors, screw tap extensions, tools with square mounts

Version:

- Housing, size 1-2, made from forged steel, size 3-7/8, welded solid-steel design, zinc-plated arm with knurling for very high loads

Advantage:

- Safe work even using high forces
- Ground and hardened steel jaws



Art. no.	13551 060
Tap wrench size	6
Suitable for min./max. square socket size	9-25 mm
Min./max. reamer cutting range	11-32 mm
Min./max. thread-cutting area, metric	9-25 mm
Length	1000 mm

EAN-Code

4039247076758