

(Material) Safety Data Sheet(M)SDS

IDENTITY (As Read on Label and Line)
43618 LR44 Alkaline Button Cell Battery

Section I

Manufacturer's Name

Draper Tools Ltd

Address (Number, Sheet, City, State, and ZIP Code)

Hursley Road
Chandlers Ford
Eastleigh
Hampshire
SO53 1YF

Telephone Number

Draper Helpline +44 (0) 2380 494344

Opening hours 8:30-17:00 Monday to Friday.

Date Prepared

03-Jan-2019

Section II – Hazardous Ingredients/Identity Information

| Hazardous Components (Specific Chemical Identity, Common Names) | (contents, %/wt) | CAS No. |
|---|------------------|------------|
| Manganese Dioxide (MnO ₂) | 29.12 | 1313-13-9 |
| Zinc (Zn) | 9.20 | 7440-66-6 |
| Potassium Hydroxide (KOH) | 3.95 | 1310-58-3 |
| Graphite (C) | 2.53 | 7782-42-5 |
| Cadmium (Cd) | <0.0005 % | 7440-43-9 |
| Mercury (Hg) | <0.0001 % | 7439-97-6 |
| Lead (Pb) | <0.002% | 7439-92-1 |
| Water (H ₂ O) | 7.03% | 7732-18-5 |
| Ferrum (Fe) | 45.343% | 8053-60-9 |
| Poly-66 (Poly) | 2.442 | 32131-17-2 |
| Nickel (Ni) | 0.383 | 14332-32-2 |

Section III – Physical/Chemical Characteristics

| | |
|---|---|
| Boiling Point KOH aqua solution = 140 °C | Specific Gravity (H ₂ O=1) MnO ₂ = 4.4, Zn = 7.1, KOH = 2.0 |
| Vapor Pressure (mmHg) KOH aqua solution = 3mmHg at 20 °C | Melting Point MnO ₂ decompose at 535 °C Zn = 420 °C, KOH aqua = -35 °C |
| Vapor Density (Air = 1) | Evaporation Rate (Butyl Acetate = 1) |
| Solubility in Water | KOH – complete |

Appearance and Color

MnO₂ is a black powder, Graphite is also a black powder, Zinc is a silver metal.
KOH aqua is a colorless liquid with stimulative order.

Section IV – Fire and Explosion Hazard Data

| | | | |
|--|-----------------------------------|-----|-----|
| Flash Point (Method Used) Incombustible | Flammable Limits Not Available | LEL | UEL |
|--|-----------------------------------|-----|-----|

Extinguishing Media: See Special Fire Fighting Procedure

Special Fire Fighting Procedure: In case of fire in an adjacent area, use water, CO₂ or dry chemical extinguishers if cells are packed in their original containers since the fuel of the fire is basically paper products. For bulk quantities of unpackaged cells use LITH-X (Graphite Base). In this case, do not use water.

As with any fire, wear self-contained breathing apparatus to avoid inhalation of hazardous decomposition products.

Unusual Fire and Explosion Hazards

Section V – Reactivity Data

| | | | |
|-----------|----------|---|--|
| Stability | Unstable | | Conditions to Avoid Do not short circuit, charge or dispose of in fire. |
| | Stable | √ | |

Incompatibility (Materials to Avoid) Hazardous polymerization will not occur.

Hazardous Decomposition or Byproducts Not Available

| | | | |
|--------------------------|----------------|---|---------------------|
| Hazardous Polymerization | May Occur | | Conditions to Avoid |
| | Will Not Occur | √ | |

Section VI – Health Hazard Data

| | | | | | | |
|--------------------|-------------|-----|-------|-----|------------|-----|
| Route(s) of Entry. | Inhalation? | Yes | Skin? | Yes | Ingestion? | Yes |
|--------------------|-------------|-----|-------|-----|------------|-----|

Health Hazards (Acute and Chronic) These chemicals are contained in a sealed can. Risk of exposure occurs, only if battery is mechanically or electrically abused. The most likely risk is acute exposure when a cell vents KOH is caustic alkali and attack the skin and eyes. Contact of electrolyte with skin and eyes should be avoided.

Section VII – Ecological Information

| | | | | | | |
|----------------|------|---------------|------------------|---------------|-----------------|---------------|
| Cardnogenicity | NTP? | Not Available | IARC Monographs? | Not Available | OSHA Regulated? | Not Available |
|----------------|------|---------------|------------------|---------------|-----------------|---------------|

Signs and Symptoms of Exposure KOH can cause chemical burn upon contact with skin.

Medical Conditions
Generally Aggravated by Exposure An acute exposure will not generally aggravate any medical help.

Section VIII – Emergency and First Aid Procedures

In case of skin contact with content of battery, flush immediately with water.
For eye contact, flush with copious amount of water for 10 minutes. If irritation persists, get medical help.

Section IX - Precautions for Safe Handling and Use

Steps to Be Taken in Case Material is Released or Spilled Wipe out by wet duster.

Section X - Waste Disposal Method

General abandonment

Section XI - Precautions to Be Taken in Handling and Storing

Avoid mechanical or electrical abuse.

Section XII - Other Precautions

Do not short circuit, charge or dispose of in fire. Battery may explode or leak.

Section XIII - Control Measures

| | | | |
|--|----------------------|----------------|--------------------------|
| Respiratory Protection (Specify Type) | | Not Available | |
| Ventilation | Local Exhaust | Not | Special Not Available |
| | Mechanical (General) | Not | Other Not Available |
| Protective Gloves | Butyl | Eye Protection | Safety Glasses |
| Other Protective Clothing or Equipment | | Not Available | |
| Work / Hygienic Practices | | Not Available | |

Section XIV – Regulatory Information

Not Available

Section XV – Other Information

Not Available

Section XVI – Transportation Information

GOLITE LR44 ALKALINE BUTTON CELL are considered to be “dry cell” batteries and are not listed as dangerous goods under below regulations:

1. Batteries, dry fulfills the requirement of U.S. Department of Transportation (DOT), Special Provision 130, i.e. they are offered for transportation in a manner that prevents the dangerous evolution of heat (for example, by the effective insulation of exposed terminals or batteries to be packed in such a way to prevent short circuits or generation of a dangerous quantity of heat.)”.
2. International Civil Aviation Administration (ICAO) and International Air Transport Association (IATA Dangerous Goods Regulation 60th Edition 2019), Special Provision A123, i.e. “An electrical battery or battery powered device having the potential of dangerous evolutions of heat that is not prepared so as to prevent a short-circuit (e.g. in the case of batteries, by the effective insulation of exposed terminals; or in the case of equipment, by disconnection of the battery and protection of exposed terminals or batteries to be packed in such a way to prevent short circuits or generation of a dangerous quantity of heat.) is forbidden from transportation.”
3. International Maritime Dangerous Goods Regulations (IMDG) 2018 edition does not regulate these batteries.

Examples of such batteries include alkali-manganese, silver oxide, zinc carbon, nickel metal hydride and nickel-cadmium batteries.
