


**BES M08MH1-PSC20B-S04G**  
**Ordering code: BES0028**

Inductive sensor  
M08x65 mm  
GlobalProx

DC, direct current  
PNP/Normally open (NO)  
Sn = 2 mm  
Flush (shielded)

**BALLUFF**  
sensors worldwide



**Characteristic data**

Eff. switching distance $S_r$	2,00 mm
Tolerance $S_r$	$\pm 10\%$
Assured operating distance $S_a$	1,60 mm
Hysteresis $H$ max. (in % of $S_r$ )	15 %
Repeat accur. $R$ max. (% of $S_r$ )	5 %
Ambient temperature	-25...70 °C
Temp. drift max. (% of $S_r$ )	10%
Switching freq. $f$ max.	700 Hz
Ready delay $t_v$ max.	30 ms
Utilisation category	DC 13
Function indicator	Yes
Power-on indicator	No
Short-circuit protected	Yes
Degree of protection as per IEC 60529	IP67
Protected against polarity reversal	Yes
Protected against reverse connection	Yes

**Electrical data**

Operating voltage	
Rated operating voltage $U_e$ DC	24,0 V
Ripple max. (% of $U_e$ )	15 %
Voltage drop static max.	2,5 V
Rated insulation voltage $U_i$	75 DC V
Effective operating current $I_e$	200 mA
No-load current $I_0$ damped	10 mA
No-load current $I_0$ undamped	5 mA

Off-state current $I_r$ max.	20 $\mu$ A
Minimum operating current $I_m$	0 mA
Rated short circuit current	100 A
Output resistance $R_a$	33.0k + D
Load capacitance max. (at $U_e$ )	1 $\mu$ F
Principle of operation	Inductive

**Mechanical data**

Housing material	CuZn
Surface protection	Nickel-plated
Sensing surface material	PA 12
Tightening torque max.	3 Nm / 6 Nm
Mounting length	45 mm
Connection type	Connector
Connector type	M12x1-S04
Shock rating	Shock, half-sinus, 30 gn, 11ms
Vibration rating	55 Hz, 1 mm ampl., 3x30 min
Degree of contamination	3

**Basic data**

Basic standard	IEC 60947-5-2
----------------	---------------

**Remarks**

The sensor is functional again after the overload has been eliminated.  
With connector, e.g. BKS-S 20-... total length = switch length +18 mm.  
Embeddable: See installation notes for inductive sensors with extended switching distance 825357.



Definitions see main catalog

subject to change

**BES M08MH1-PSC20B-S04G**  
Ordering code: **BES0028**

Inductive sensor  
M08x65 mm  
GlobalProx

DC, direct current  
PNP/Normally open (NO)  
Sn = 2 mm  
Flush (shielded)

**BALLUFF**  
*sensors worldwide*

