

PLUG-IN RELAY, 3 CO CONTACTS, 125V DC, 10A,
WIDTH 22.5MM ALSO FOR LZS BASES

General technical data:

Type of voltage		DC
Control supply voltage		
<ul style="list-style-type: none"> • for DC Rated value — minimum — maximum 	V V	125 125
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		3
Operating current of the auxiliary contacts		
<ul style="list-style-type: none"> • at DC-13 — at 24 V • at AC-15 — at 230 V 	A A	8 5
Design of the switching function positively driven		No
Switching behavior		monostable

Mechanical data:

Type of electrical connection		screw-type terminals
Design of the relay operating mechanism		poled
Product component Plug-in socket		No
Width	mm	22.5
Height	mm	28
Depth	mm	35

Certificates/ approvals:

General Product Approval

other



[Declaration of Conformity](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=LZX:PT370125>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/LZX:PT370125>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=LZX:PT370125&lang=en

last modified:

15.01.2015