XCKS541

limit switch XCKS - th.plastic roller lever var. length - 1NC+1NO - slow - Pg13





Main Range of product OsiSense XC Series name Standard format Product or component Limit switch type XCKS Device short name Sensor design Body type Fixed Head type Rotary head Material Plastic Body material Plastic Head material Plastic Fixing mode By the body Movement of operating Rotary head Type of operator Spring return roller lever thermoplastic variable Type of approach Lateral approach, 1 or 2 programmable direction Cable entry 1 entry tapped for Pg 13.5 cable gland, cable outer diameter: 9...12 mm Number of poles 2 Contacts type and 1 NC + 1 NO composition

Slow-break, break before make

Complementary

By 30° cam
Screw-clamp terminals, clamping capacity: 1 x 0.52 x 2.5 mm ²
Zb
1
With
0.89 lbf.in (0.1 N.m)
6 m/min
1.5 m/s
A300, AC-15 (Ue = 240 V), Ie = 3 A conforming to EN/IEC 60947-5-1 appendix A Q300, DC-13 (Ue = 250 V), Ie = 0.27 A conforming to EN/IEC 60947-5-1 appendix A
10 A AC
300 VUL 508 500 V 3)IEC 60947-1 300 VCSA C22.2 No 14
25 MOhm IEC 60255-7 category 3
6 KV IEC 60664 6 kV IEC 60947-1
0 KV 1EO 00047-1
10 A cartridge fuse, type gG
2.11.11.2.2.2.11.1

Contact operation

Maximum Width	1.57 in (40 mm)
Height	4.616.77 in (117172 mm)
Depth	2.24 in (57 mm)
Net Weight	0.36 lb(US) (0.165 kg)
Terminals description ISO n°1	(13-14)NO (21-22)NC

Environment

Shock resistance	50 gn 11 ms IEC 60068-2-27
Vibration resistance	25 gn 10500 Hz)IEC 60068-2-6
IP degree of protection	IP67 IEC 60529 IP66 IEC 60529
IK degree of protection	IK05 conforming to EN 50102
Electrical shock protection class	Class II IEC 61140 Class II NF C 20-030
Overvoltage category	Class II conforming to IEC 61140 Class II NF C 20-030
Ambient air temperature for operation	-13158 °F (-2570 °C)
Ambient air temperature for storage	-40158 °F (-4070 °C)
Protective treatment	TC
Product certifications	CCC CSA UL
Standards	CENELEC EN 50041 EN 60204-1 UL 508 CSA C22.2 No 14 EN 60947-5-1 IEC 60204-1 IEC 60947-5-1

Ordering and shipping details

Category	22417 - LIMIT SWITCH, IEC, CLASSIC	
Discount Schedule	Т	
GTIN	03389110646962	
Nbr. of units in pkg.	1	
Package weight(Lbs)	0.36 lb(US) (0.16 kg)	
Returnability	No	
Country of origin	ID	

Packing Units

Package 1 Height	0.400 dm
Package 1 width	1.300 dm
Package 1 Length	0.600 dm


Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Circulatily Fiolile	End Of Life Information

Warranty 18 months

XCKS541

Dimensions




- 1 tapped entry for Pg 13.5 cable gland 2 elongated holes \varnothing 5.3 x 7.3.

XCKS541

Mounting with Cable Entry

Position of Cable Gland







- (1) Recommended
- (2) To be avoided

Mounting with Rotary Heads and Levers

Type of Cam






- (1) Recommended
- (2) To be avoided

Setting-up

Head Rotation Adjustment



C: 1 Nm (+/- 20%) / 8.85 lb-in (+/- 20%)

Setting-up


Lever Angle Adjustment



C: 1 Nm (+/- 20%) / 8.85 lb-in (+/- 20%)

Setting-up with Head ZCKD05

Direction of Actuation Programming



C: 1 Nm (+/- 20%) / 8.85 lb-in (+/- 20%)

Wiring Diagram

2-pole NC + NO Break Before Make, Slow Break

Product data sheet **Technical Description**


XCKS541

Characteristics of Actuation

Switch Actuation by 30° Cam



Functionnal Diagram



- Closed
- (1) (2) Open