

Morse taper mount shape F with flat tangs

ORION[®]

Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm²
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground

Art. no.	22778 175
Brand	ORION
Manufacturer Part Number	22778175
VDI mount diameter	40 mm
Morse taper size	MK 2
Diameter	17.78 mm
Projecting length	22 mm
Outer diameter	55 mm
Collar diameter	83 mm
Height	32.5 mm
Length	36 mm
Gross Weight	1.582 kg
Product Group	2AC



EAN

4053625465620