

Swarf containers, tip from the forklift operator's seat

Carrying capacity up to 1250 kg, mobile with roll-off system

Application:

For the collection and separation of liquids from solids and for the transport or disposal of all types of waste, bulk materials, chips and mass-produced parts.

Execution:

- Stable base frame with rollers, sliding handle and fork pockets
- Sheet metal tray with surrounding edge profile, welded oil-resistant and watertight
- Screen plate, hole diameter 3 mm, partition 6 mm, drain valve 1" for draining off liquids
- Protection against accidental slipping and tipping
- Mobile with wheels made of polyamide

Advantage:

- Particularly suitable for collecting chippings
- Favourable load centre, tilting at any height using a wire rope, anti-roll-off mechanism ensures convenient forwards and backwards tipping from the forklift seat
- Mobile thanks to wheels which mean it can be used everywhere

Delivery:

Goods supplied without packaging as standard. Packaging available for an additional charge.



Art. no.	50266 206
Volume	0.5 m ³
Length	1275 mm
Width	1280 mm
Tipper edge height	690 mm
Height	820 mm
Fork pocket clearance	30 mm
Fork pocket size (W x H)	200 x 70 mm
Number of wheels	4 PCS
With drain valve	Yes
With stacker seat tilt function	Yes
With perforated sheet	Yes
Load-carrying capacity	1000 kg
Surface	Lacquered
Colour	Optional
Gross Weight	145.000 kg
Product Group	5AI