

Beacon LED Shelf

Beacon SHELF 4K L3 BLK
2093077



Product features

- 2093077 Beacon SHELF 4K L3 BLK is an Integrated LED spotlight, black RAL 9005, compact and minimalist design, ideal for retail and display applications, die-cast aluminium body, passive cooling heatsink, uniform vertical illuminance, beam angle: asymmetric, optics: asymmetric aluminium reflector, colour temperature: 4000K neutral white, total system power: 48W, total fixture output: 4485lm, luminaire efficacy: 93lm/W, LOR: 100%, colour rendering: Ra 93 typical, LED Chromacity: 3 step MacAdam ellipse, lifetime: 50,000 hours at 70% of the original output (L70), energy class: A++, A+, A, IR/UV free light source without heat radiation, operating voltage: 220-240V / 50-60Hz, drive current: 1200mA, electronic driver, non dimmable, power factor: 0.98, electrical protection: CLASS I, 3-circuit track adaptor, suitable for Concord Lytespan 3 track, ingress protection rating: IP20, suitable for internal environment only, horizontal rotation: 355°, vertical tilt: 90°, lockable positioning using Allen key, dimensions: Ø1...



PRODUCT OVERVIEW

| | |
|-----------------------------|------------------------|
| Product name | Beacon SHELF 4K L3 BLK |
| Technology | LED |
| Housing | Aluminium |
| Mount | Track mounting |
| Environment | Internal |
| General application | Retail |
| ETIM Class | EC001744 |
| E-number FI | 4237867 |
| Warranty | 5 years |
| Fixture luminous flux (lm) | 4485 |
| Luminaire efficacy (lm/W) | 93 |
| LOR (%) | 100 |
| Colour temperature (K) | 4000 |
| Light colour | Neutral White |
| CRI (Ra) | 93 |
| Colour Consistency (SDCM) | 3 |
| Photobiological Risk Group | RG1 |
| Total power consumption (W) | 48 |
| Product Voltage (V) | 240 |
| Electrical protection | Class I |
| Control gear type | Electronic ballast |
| Dimming method | N/A |
| Housing colour | Black |
| IP rating | IP20 |
| Product EAN number | 5025768930777 |

DATA TABLE

General data

| | |
|--------------|------------------------|
| Product name | Beacon SHELF 4K L3 BLK |
|--------------|------------------------|

Beacon LED Shelf

Beacon SHELF 4K L3 BLK
2093077

| | |
|---|----------------|
| Technology | LED |
| Housing | Aluminium |
| Mount | Track mounting |
| Environment | Internal |
| General application | Retail |
| Performance ambient temperature Tq (°C) | 25 |
| ETIM Class | EC001744 |
| E-number FI | 4237867 |
| Warranty | 5 years |

Optical data

| | |
|----------------------------|---------------|
| Fixture luminous flux (lm) | 4485 |
| Luminaire efficacy (lm/W) | 93 |
| LOR (%) | 100 |
| Colour temperature (K) | 4000 |
| Light colour | Neutral White |
| CRI (Ra) | 93 |
| Colour Consistency (SDCM) | 3 |
| Adjustable chromaticity | N |
| Photobiological Risk Group | RG1 |

Electrical data

| | |
|--|--------------------|
| Total power consumption (W) | 48 |
| Mains voltage (V) | 220-240V |
| Product Voltage (V) | 240 |
| Lamp power factor | 0.98 |
| Electrical protection | Class I |
| Control gear type | Electronic ballast |
| Transformer required | Yes |
| Dimming method | N/A |
| Drive current (mA) | 1200 |
| Energy Efficiency Class (A->G) of contained light source | E |

Physical data

| | |
|-------------------------------|------------------|
| Housing colour | Black |
| IP rating | IP20 |
| Diffuser finish | Transparent |
| Diffuser material | PC Polycarbonate |
| Nominal Product Length (mm) | 85 |
| Nominal Product Width (mm) | 170 |
| Nominal Product Height (mm) | 227 |
| Nominal Product Diameter (mm) | 110 |
| Weight (kg) | 1.4 |

Packaging


| | |
|---------------------------------------|---------------|
| Single packaging type | Carton |
| Product EAN number | 5025768930777 |
| Packaging single length / height (cm) | 25.0 |

Beacon LED Shelf

Beacon SHELF 4K L3 BLK
2093077

| | |
|--------------------------------------|----------------|
| Packaging single width (cm) | 19.5 |
| Packaging single depth (cm) | 20.0 |
| DUN14 (outer) | 05025768930777 |
| Units per outer package | 1 |
| Packaging outer length / height (cm) | 25.0 |
| Packaging outer width (cm) | 19.5 |
| Packaging outer depth (cm) | 20.0 |

PHOTOMETRY



TECHNICAL DRAWINGS

