

Hinged-door cabinet housing with doors with viewing window, height 1950 mm

Cabinet housing without internal configuration

Application:

For secure and clearly-visible storage of tools, accessories, files or many other parts.

Execution:

- Robust sheet steel structure
- Integrated mounting profile enables height adjustment of accessories in the grid of 30 mm
- Forklift-compatible base with removable base fascia for transporting internally
- Can be locked using grip handle and cylinder security lock incl. 2 keys
- cabinet can be fitted with an ELECTRONIC CODE combination lock at extra charge as an option, see no. 50392 020
- Accessories for equipping with support profiles: 3 support profiles no. 50658 110-158 can be inserted per storage level. One pair of guide rails no. 50658 100 is required per storage level. Please consider when ordering.
- Accessories such as pairs of support rails, support profiles, drawers on the following pages

Advantage:

- Using the mounting profile in the cabinet, can be optionally expanded and customised with accessories such as support profiles, drawers, shelves and perforated sheet panels



Art. no.	50658 009
Brand	HK
Manufacturer Part Number	50658009
Door design	Inspection glass
Height	1950 mm
Width	1018 mm
Depth	620 mm
Effective height	1770 mm
Load-carrying capacity	1000 kg
With doors	Yes
Central locking	Yes
Lock type	DOM® locking system
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Anthracite grey RAL 7016
Surface	Powder-coated
Gross Weight	100.000 kg
Product Group	507

EAN

4053625406340