

# FO converters - FL MC 2000T SM20 SC



2891317

<https://www.phoenixcontact.com/pc/products/2891317>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



FO converter with SC duplex fiber optic connection (1300 nm), for converting 100Base-TX to single mode fiberglass with a maximum FO segment length of 20 km. Auto MDI(X) function and comprehensive link diagnostics. DIN rail mountable with wide operating temperature range.

## Commercial Data

Item number	2891317
Packing unit	1 pc
Minimum order quantity	1 pc
Product Key	DNC312
Catalog Page	Page 353 (C-6-2019)
GTIN	4046356869591
Weight per Piece (including packing)	310.5 g
Weight per Piece (excluding packing)	302.3 g
Customs tariff number	85176200
Country of origin	TW

## Technical Data

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Product properties

Product type	Media converter
MTTF	77.82 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
Signal delay	865 ns (Pass-through mode) 835 ns (Auto converter mode, 100 Mbps, static)

### Electrical properties

Electrical isolation	VCC // FE // Ethernet
Test voltage data interface/power supply	1500 V AC (500 V AC, 1 minute)

#### Supply

Supply voltage range	12 V DC ... 48 V DC
Nominal supply voltage	24 V DC
Typical current consumption	110 mA (24 V DC)
Connection method	Plug-in screw terminal block (COMBICON), redundancy possible

### Output data

Output name	Relay output
Output description	Alarm output
Number of outputs	1
Contact type	N/C contact
Maximum switching voltage	24 V DC
Max. switching current	100 mA

### Connection data

#### Supply

Connection method	Plug-in screw terminal block (COMBICON), redundancy possible
-------------------	--

### Interfaces

Signal	Ethernet
--------	----------

#### Data: optical FO

Transmission length incl. 3 dB system reserve	20 km (fiberglass with F-G 9/125 0.36 dB/km)
Connection method	SC duplex
Wavelength	1310 nm
Transmission medium	Single-mode fiberglass

2891317

<https://www.phoenixcontact.com/pc/products/2891317>

Data: Ethernet interface, 10/100Base-T(X) in accordance with IEEE 802.3

Data rate	10/100 Mbps
Serial transmission speed	10/100 Mbps
Connection method	RJ45 jack, shielded
No. of channels	1
Transmission length	100 m (twisted pair, shielded)
Transmission medium	Copper
Signal LEDs	LNK/ACT, 100
Auto-negotiation modes	Auto
Link through	Link fault pass through
MDI-/MDI-X switchover	Auto-MDI(X)

## Dimensions

Width	28 mm
Height	110 mm
Depth	70 mm

## Material specifications

Housing material	Aluminum
------------------	----------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	4850 m
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock	300 m/s <sup>2</sup> , 11 ms (IEC 60068-2)
Air pressure (operation)	66 kPa ... 108 kPa
Air pressure (storage/transport)	66 kPa ... 108 kPa

## Approval data

### Conformity/Approvals

Conformance	CE-compliant
UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

### Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

### Electrostatic discharge

# FO converters - FL MC 2000T SM20 SC



2891317

<https://www.phoenixcontact.com/pc/products/2891317>

Comments	Criterion B
Electromagnetic HF field	
Standards/regulations	EN 61000-4-3
Electromagnetic HF field	
Comments	Criterion A
Fast transients (burst)	
Standards/regulations	EN 61000-4-4
Fast transients (burst)	
Comments	Criterion A
Surge current load (surge)	
Standards/regulations	EN 61000-4-5
Surge current load (surge)	
Comments	Criterion B
Conducted interference	
Standards/regulations	EN 61000-4-6
Conducted interference	
Comments	Criterion A
Emitted interference	
Standards/regulations	EN 55032

## Mounting

Mounting type	DIN rail mounting
Mounting position	On horizontal DIN rail NS 35 in acc. with EN 60715

2891317

<https://www.phoenixcontact.com/pc/products/2891317>

## Approvals



**UL Listed**

Approval ID: FILE E 140324



**cUL Listed**

Approval ID: FILE E 140324



**cUL Listed**

Approval ID: FILE E 199827



**UL Listed**

Approval ID: FILE E 199827

**cULus Listed**

**cULus Listed**

# FO converters - FL MC 2000T SM20 SC



2891317

<https://www.phoenixcontact.com/pc/products/2891317>

## Classifications

### ECLASS

ECLASS-9.0	19170114
ECLASS-10.0.1	19170132
ECLASS-11.0	19170411

### ETIM

ETIM 8.0	EC001467
----------	----------

### UNSPSC

UNSPSC 21.0	43201500
-------------	----------

# FO converters - FL MC 2000T SM20 SC



2891317

<https://www.phoenixcontact.com/pc/products/2891317>

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 10; For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

2891317

<https://www.phoenixcontact.com/pc/products/2891317>

## Accessories

### PCB connector

PCB connector - MSTB 2,5/ 8-ST - 1754562

<https://www.phoenixcontact.com/pc/products/1754562>



PCB connector, nominal cross section: 2.5 mm<sup>2</sup>, color: green, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Tin, type of contact: Female connector, number of potentials: 8, number of rows: 1, number of positions: 8, number of connections: 8, product range: MSTB 2,5/...-ST, pitch: 5 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, locking clip: - Locking clip, plug-in system: COMBICON MSTB 2,5, locking: without, mounting: without, type of packaging: packed in cardboard

---

### Port Guard Security Element

Port Guard Security Element - FL PATCH GUARD - 2891424

<https://www.phoenixcontact.com/pc/products/2891424>



Lockable security element



2891317

<https://www.phoenixcontact.com/pc/products/2891317>

## Key

Key - FL PATCH GUARD KEY - 2891521

<https://www.phoenixcontact.com/pc/products/2891521>

Key for lockable security element



---

## Surge protection device

Surge protection device - DT-LAN-CAT.6+ - 2881007

<https://www.phoenixcontact.com/pc/products/2881007>



Surge protection in accordance with Class E<sub>A</sub> (CAT6<sub>A</sub>), for Gigabit Ethernet (up to 10 Gbps), token ring, FDDI/CDDI, ISDN, and DS1. Suitable for Power over Ethernet (PoE++ / 4PPoE) "Mode A" and "Mode B". RJ45 attachment plug with separate grounding cable and ground connection snap-on foot for NS 35 DIN rails.

# FO converters - FL MC 2000T SM20 SC



2891317

<https://www.phoenixcontact.com/pc/products/2891317>

## DIN rail adapter

DIN rail adapter - FL DIN RA - 2891053

<https://www.phoenixcontact.com/pc/products/2891053>

The FL DIN RA is installed in a standard, 19-inch rack (EIA-310-D, IEC 60297-3-100) to allow DIN rail mounted equipment to be rack mounted.




---

## Dust protection

Dust protection - FL RJ45 PROTECT CAP - 2832991

<https://www.phoenixcontact.com/pc/products/2832991>

Dust protection caps for RJ45 socket



# FO converters - FL MC 2000T SM20 SC

2891317

<https://www.phoenixcontact.com/pc/products/2891317>




## End clamp

End clamp - E/NS 35 N - 0800886

<https://www.phoenixcontact.com/pc/products/0800886>

End clamp, width: 9.5 mm, color: gray



---

## Patch cable

Patch cable - FL CAT5 PATCH 0,5 - 2832263

<https://www.phoenixcontact.com/pc/products/2832263>

Patch cable, CAT5, assembled, 0.5 m



2891317

<https://www.phoenixcontact.com/pc/products/2891317>

## Patch cable

Patch cable - FL CAT5 PATCH 1,0 - 2832276

<https://www.phoenixcontact.com/pc/products/2832276>

Patch cable, CAT5, assembled, 1 m



---

## Patch cable

Patch cable - FL CAT5 PATCH 2,0 - 2832289

<https://www.phoenixcontact.com/pc/products/2832289>

Patch cable, CAT5, assembled, 2 m




2891317

<https://www.phoenixcontact.com/pc/products/2891317>

## Patch cable

Patch cable - NBC-R4AC-R4AC-IE8A/.../... - 1411854

<https://www.phoenixcontact.com/pc/products/1411854>




Patch cable, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, cable outlet: straight, Ethernet

---

## Patch cable

Patch cable - NBC-R4AC/10G-R4AC/10G-94F/2,0 - 1408360

<https://www.phoenixcontact.com/pc/products/1408360>



Patch cable, CAT6<sub>A</sub>, 4-pair, shielded, connection not crossed (line), assembled at both ends with RJ45/IP20 connectors, outer sheath material: PUR, length: 2.0 m


2891317

<https://www.phoenixcontact.com/pc/products/2891317>

## Patch cable

Patch cable - NBC-R4AC/10G-R4AC/10G-94F/3,0 - 1408365

<https://www.phoenixcontact.com/pc/products/1408365>



Patch cable, CAT6<sub>A</sub>, 4-pair, shielded, connection not crossed (line), assembled at both ends with RJ45/IP20 connectors, outer sheath material: PUR, length: 3.0 m

---

## Patch cable

Patch cable - NBC-R4AC/1,0-93B/R4AC - 1408968

<https://www.phoenixcontact.com/pc/products/1408968>



Patch cable, degree of protection: IP20, cable length: 1 m, number of positions: 4, 100 Mbps, CAT5, material: PA 6.6, PROFINET

# FO converters - FL MC 2000T SM20 SC



2891317

<https://www.phoenixcontact.com/pc/products/2891317>

## Patch cable

Patch cable - NBC-R4AC/2,0-93B/R4AC - 1408969

<https://www.phoenixcontact.com/pc/products/1408969>



Patch cable, degree of protection: IP20, cable length: 2 m, number of positions: 4, 100 Mbps, CAT5, material: PA 6.6, PROFINET

---

## Patch cable

Patch cable - NBC-R4AC/5,0-93B/R4AC - 1408970

<https://www.phoenixcontact.com/pc/products/1408970>



Patch cable, degree of protection: IP20, cable length: 5 m, number of positions: 4, 100 Mbps, CAT5, material: PA 6.6, PROFINET

# FO converters - FL MC 2000T SM20 SC



2891317


<https://www.phoenixcontact.com/pc/products/2891317>

## FO patch cable

FO patch cable - FOC-SC:PA-SC:PA-OS2:D01/1 - 1115550

<https://www.phoenixcontact.com/pc/products/1115550>

Single-mode OS2 duplex jumper, SC-SC, UPC polishing, length 1 m




---

## FO patch cable

FO patch cable - FOC-SC:PA-SC:PA-OS2:D01/2 - 1115548

<https://www.phoenixcontact.com/pc/products/1115548>

Single-mode OS2 duplex jumper, SC-SC, UPC polishing, length 2 m





# FO converters - FL MC 2000T SM20 SC



2891317


<https://www.phoenixcontact.com/pc/products/2891317>

## FO patch cable

FO patch cable - FOC-ST:PA-SC:PA-OS2:D01/1 - 1115582

<https://www.phoenixcontact.com/pc/products/1115582>

Single-mode OS2 duplex jumper, ST-SC, UPC polishing, length 1 m




---

## FO patch cable

FO patch cable - FOC-ST:PA-SC:PA-OS2:D01/2 - 1115581

<https://www.phoenixcontact.com/pc/products/1115581>

Single-mode OS2 duplex jumper, ST-SC, UPC polishing, length 2 m



# FO converters - FL MC 2000T SM20 SC



2891317


<https://www.phoenixcontact.com/pc/products/2891317>

## FO patch cable

FO patch cable - FOC-LC:PA-SC:PA-OS2:D01/1 - 1115618

<https://www.phoenixcontact.com/pc/products/1115618>

Single-mode OS2 duplex jumper, LC-SC, UPC polishing, length 1 m




---

## FO patch cable

FO patch cable - FOC-LC:PA-SC:PA-OS2:D01/2 - 1115617

<https://www.phoenixcontact.com/pc/products/1115617>

Single-mode OS2 duplex jumper, LC-SC, UPC polishing, length 2 m



---

Phoenix Contact 2022 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstraße 8  
D-32825 Blomberg  
+49 (0) 5235-3 00  
[info@phoenixcontact.com](mailto:info@phoenixcontact.com)